



SECTION

Industrial switches

Industrial grade AC toggle switches

Product description

Single-pole, double-pole, 3-way, 4-way

15A, 120/277V/AC; 15A, 347V/AC

20A, 120/277V/AC; 20A, 347V/AC; 30A, 120/277V/AC

Premium industrial grade AC toggle switches, back & side wire



Rating A	V/AC	Description	Color suffix	Catalog no.				
15	120/277	Single-pole, toggle	B, GY, RD, V, W	□ AH1201__	•	•	•	•
		Double-pole toggle	B, GY, V, W	□ AH1202__	•	•	•	•
		3-Way, toggle	B, GY, RD, V, W	□ AH1203__	•	•	•	•
		4-Way, toggle	B, GY, V, W	□ AH1204__	•	•	•	•
20	120/277	Single-pole, toggle	B, BK, GY, LA, RD, V, W	□ AH1221__	•	•	•	•
		Double-pole toggle	B, GY, RD, V, W	□ AH1222__	•	•	•	•
		3-Way, toggle	B, BK, GY, LA, RD, V, W	□ AH1223__	•	•	•	•
		4-Way, toggle	B, BK, GY, LA, RD, V, W	□ AH1224__	•	•	•	•
30	120/277	Single-pole, toggle	B, RD, V, W	□ 3031__*	•	•	•	•
		Double-pole toggle	B, RD, V, W	□ 3032__*	•	•	•	•

* Not NOM cert

Industrial grade AC toggle switches, back & side wire



Rating A	V/AC	Description	Color suffix	Catalog no.				
15	120/277	Single-pole, lighted toggle	V, W	□ AH1201LT__	•	•	•	•
		3-Way, lighted toggle	V, W	□ AH1203LT__	•	•	•	•
		Single-pole, pilot lighted red toggle	RD	□ AH1201PL	•	•	•	•
		Double-pole, pilot lighted red toggle	RD	□ AH1202PL	•	•	•	•
20	120/277	Single-pole, lighted toggle	V, W	□ AH1221LT__	•	•	•	•
		3-Way, lighted toggle	V, W	□ AH1223LT__	•	•	•	•
		Single-pole, pilot lighted red toggle	RD	□ AH1221PL	•	•	•	•
		Double-pole, pilot lighted red toggle	RD	□ AH1222PL	•	•	•	•
30	120/277	Double-pole, pilot lighted red toggle	RD	□ 3032PL*	•	•	•	•

* Not NOM cert

Industrial grade AC toggle switches, back & side wire



Rating A	V/AC	Description	Color suffix	Catalog no.				
15	347	Single-pole, Canadian voltage toggle	B, I, W	□ AH18201__«	•	•		
		Double-pole, Canadian voltage toggle	B, I	□ AH18202__«	•	•		
		3-Way, Canadian voltage toggle	B, I, W	□ AH18203__«	•	•		
20	347	Single-pole, Canadian voltage toggle	B, I, W	□ AH18221__«	•	•		
		Double-pole, Canadian voltage toggle	B, I	□ AH18222__«	•	•		
		3-Way, Canadian voltage toggle	B, I, W	□ AH18223__«	•	•		

« No Color suffix = Brown, I = Ivory

Color ordering information:

For ordering devices, include Catalog no. Followed by the Color suffix: B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V or I (Ivory), W (White)

B	BK	GY	LA	RD	V or I	W
(Brown)	(Black)	(Gray)	(Lt. Almond)	(Red)	(Ivory)	(White)

Specification information: 120/277V Industrial: E-36, 120/277V industrial ArrowLink modular: E-43

Compliances, specifications and availability are subject to change without notice.



ArrowLink option available. Add "M" suffix to Standard catalog number (example AH1201B, AH1201BM). For ordering information on ArrowLink & ArrowLink SPD connectors, see Page E-4



Build-to-spec customizable devices - Page A-6



RoHS compliant - Page Q-30

