

RhinoBox temporary power centers accessories

Product description

50A input
20A, 30A, 50A output
120/240 V/AC (max.)



PC50AE

Features

- Use to connect RhinoBox to power sources and to additional RhinoBoxes in series
- Pro grip's tough nylon device housing resists impact in harsh environments
- Insulated body on cord sets for extra measure of safety
- Powerful cord-gripping capability helps eliminate conductor cord grip slip and strain on terminals

Pro grip cord sets & adapters

Rating A	V/AC	Cord length	Description	Plug (male)	Plug (female)	Catalog no.	
50	125/250	50 ft.	California style devices, E-series 6/4 flexible black extension cord	 CS6365EX	 CS6364EX	<input type="checkbox"/> PC50AE	•
		100 ft.	California style devices, E-series 6/4 flexible black extension cord	 CS6365EX	 CS6364EX	<input type="checkbox"/> PC50BE	•
		50 ft.	California style devices, 6/4 flexible black UL extension cord	 CS6365EX	 CS6364EX	<input type="checkbox"/> PC50A	•
		100 ft.	California style devices, 6/4 flexible black UL extension cord	 CS6365EX	 CS6364EX	<input type="checkbox"/> PC50B	•
		4 ft.	Non-NEMA 6/4 flexible black blank/bare wire connector	—	 CS6364EX	<input type="checkbox"/> PA50-6	•
		4 ft.	NEMA 14-30P to 50A straight blade to 50A locking non-NEMA adapter	 5732AN	 CS6364EX	<input type="checkbox"/> A304WCSF	•
		4 ft.	NEMA 14-50P to 50A straight blade to 50A locking non-NEMA adapter	 5752AN	 CS6364EX	<input type="checkbox"/> A504WCSF	•

RhinoBox replacement devices

Description	Catalog no.
20A GFCI module (manual reset)	<input type="checkbox"/> 20GFMODM
20A GFCI module (automatic reset)	<input type="checkbox"/> 20GFMODA
50A 125/250V locking outlet	<input type="checkbox"/> CS6369
50A outlet flip cover (black)	<input type="checkbox"/> 7788BK
30A locking receptacle	<input type="checkbox"/> CWL630R
20A/30A locking receptacle flip cover (gray)	<input type="checkbox"/> WP2
20A locking receptacle	<input type="checkbox"/> CWL520R
20A/30A locking receptacle flip cover (black)	<input type="checkbox"/> WP2BK-1
20A single straight blade receptacle	<input type="checkbox"/> 1877BK
Duplex receptacle damp location cover	<input type="checkbox"/> S1962BK-P
20A duplex receptacle, weather-resistant (black)	<input type="checkbox"/> WRBR20BK

Testing & code compliance: Pro-Grip plug & connector listed to UL498, file no. E3663. PC50A & PC50B Cord listed UL 62. cUL Certified to CSA 22.2 no. 42. ANSI/UL498-2008. NOM certified **Material characteristics:** Pro grip cord sets: outer shell: impact-modified nylon. Interior body: glass-filled nylon. Terminal clamps & screws: brass alloy, zinc-plated. Gasket: neoprene rubber. **Compliances, specifications and availability are subject to change without notice.**