

Portable outlet boxes, cover plates & kits accessories

Standard depth box, extra depth box, feed through box, portable outlet box covers

Features

- Innovative one-piece design incorporates integrated strain relief and cover plate mounting holes (standard depth only)
- Rugged Alcryn® and Valox® materials provide durability in industrial applications
- Variety of standard and flip lid cover plates available for customized installations
- Non-conductive Alcryn® material provides protection against electric shock
- Large internal volume for ease of wiring



WD3059



WD3099




Cover plates




WD3059-DDN


Portable outlet boxes

Description	Color	Catalog no.	
Standard depth	Y	<input type="checkbox"/> WD3059 ^{OOA}	•
Extra depth	Y	<input type="checkbox"/> WD3099 ^{OOA}	•
Extra depth feed through	Y	<input type="checkbox"/> WD3090F ^{OO}	•

Portable outlet box cover plates

Description	Diameter opening	Color	Catalog no.	
Duplex receptacle	–	BK	<input type="checkbox"/> WD3051BK	•
Single receptacle	1.56" (3.96mm)	BK	<input type="checkbox"/> WD3052BK	•
Single receptacle	1.39" (3.53mm)	BK	<input type="checkbox"/> WD3054BK	•
Decorator style	–	BK	<input type="checkbox"/> WD3055BK	•
Decorator style with flip lid	–	BK	<input type="checkbox"/> WD3056BK	•
Duplex receptacle with flip lid	–	BK	<input type="checkbox"/> WD3060BK	•
Blank plate	–	BK	<input type="checkbox"/> WD3061BK	•

Portable outlet box & cover plate kits


Description	Cover plate type	Catalog no.	
Standard depth	(2) Duplex receptacle	<input type="checkbox"/> WD3059-DDN ^{OOA}	•
Standard depth	(2) Duplex receptacle with flip lid	<input type="checkbox"/> WD3059-DDW ^{OOA}	•
Standard depth	(2) Single receptacle, dia.-1.39" (3.53mm)	<input type="checkbox"/> WD3059-SSN ^{OOA}	•
Standard depth	(2) Single receptacle, dia.-1.56" (3.96mm)	<input type="checkbox"/> WD3059-LLN ^{OOA}	•
Extra depth	(2) Duplex receptacle	<input type="checkbox"/> WD3099-DDN ^{OO}	•
Extra depth	(2) Duplex receptacle with flip lid	<input type="checkbox"/> WD3099-DDW ^{OO}	•
Extra depth	(2) Single receptacle, dia.-1.39" (3.53mm)	<input type="checkbox"/> WD3099-SSN ^{OO}	•
Extra depth	(2) Single receptacle, dia.-1.56" (3.96mm)	<input type="checkbox"/> WD3099-LLN ^{OO}	•
Extra depth feed through	(2) Duplex receptacle	<input type="checkbox"/> WD3090F-DDN ^{OO}	•
Extra depth feed through	(2) Duplex receptacle with flip lid	<input type="checkbox"/> WD3090F-DDW ^{OO}	•
Extra depth feed through	(2) Single receptacle, dia.-1.39" (3.53mm)	<input type="checkbox"/> WD3090F-SSN ^{OO}	•
Extra depth feed through	(2) Single receptacle, dia.-1.56" (3.96mm)	<input type="checkbox"/> WD3090F-LLN ^{OO}	•

^{OO}Noted Cat. nos. are Yellow boxes, also available in All-Black. For ordering Black, include Cat. no. followed by the color code: BK
^ΔcULus Listed

All Eaton's Wiring Devices' Portable Outlet Boxes have compression fittings. Alcryn® is a registered trademark of Advanced Polymer Alloys, a subsidiary of Ferro Corporation. Valox® is a registered trademark of the GE Company.

Color information:

BK (Black), Y (Yellow)



Material characteristics: Flammability: Meets UL94 requirements, V0 rated. Environmental: Corrosion resistant, weather resistant to impact, heat, weather, oils, chemical, shock & UV exposure. Temperature rating: -35°C to 80°C (-31°F to 176°F).

Compliances, specifications and availability are subject to change without notice.