

Pulling grips

Slack-double weave

Product description

Standard & long length, offset eye

Features & applications

- Slack grips feature an offset eye for easy attachment to the pulling line
- High strength galvanized steel wire mesh
- Used when cable end is accessible
- Single offset eye easily mates to swivel and line type connectors as well as easy attachment to pull line
- Used in factory maintenance and construction, utility work and replacement of underground cable
- Slack grips are reusable grips used for pulling slack in underground cable preparatory to final placement
- Also used for cable removal



SKT15017



SKT15025

Standard length, offset eye



Cord diameter	Mesh length	Approx. break strength†	Catalog no.*	
0.75-0.99" (19.1-25.1mm)	13" (330.2mm)	3,000 lbs.	☐ SKT7512	•
1.00-1.24" (25.4-31.2mm)	16" (406.4mm)	4,200 lbs.	☐ SKT10015	•
1.25-1.49" (31.8-37.8mm)	17" (431.8mm)	5,500 lbs.	☐ SKT12516	•
1.50-1.74" (38.1-44.2mm)	18" (457.2mm)	7,400 lbs.	☐ SKT15017	•
1.75-1.99" (44.5-50.5mm)	19" (482.6mm)	11,000 lbs.	☐ SKT17518	•
2.00-2.49" (50.8-63.3mm)	20" (508.0mm)	11,000 lbs.	☐ SKT20019	•
2.50-2.99" (63.5-76.0mm)	21" (533.4mm)	11,000 lbs.	☐ SKT25020	•
3.00-3.49" (76.2-88.6mm)	22" (558.8mm)	16,000 lbs.	☐ SKT30021	•
3.50-3.99" (88.9-101.3mm)	23" (584.2mm)	16,000 lbs.	☐ SKT35022	•

Long length, offset eye



Cord diameter	Mesh length	Approx. break strength†	Catalog no.*	
0.75-0.99" (19.1-25.1mm)	21" (533.4mm)	3,000 lbs.	☐ SKT7520	•
1.00-1.24" (25.4-31.2mm)	21" (533.4mm)	5,500 lbs.	☐ SKT10020	•
1.25-1.49" (31.8-37.8mm)	24" (609.6mm)	5,500 lbs.	☐ SKT12523	•
1.50-1.74" (38.1-44.2mm)	26" (660.4mm)	7,400 lbs.	☐ SKT15025	•
2.00-2.49" (50.8-63.3mm)	27" (685.8mm)	11,000 lbs.	☐ SKT20026	•
2.50-2.99" (63.5-76.0mm)	30" (762.0mm)	11,000 lbs.	☐ SKT25029	•
3.00-3.49" (76.2-88.6mm)	33" (838.2mm)	16,000 lbs.	☐ SKT30032	•
3.50-3.99" (88.9-101.3mm)	36" (914.4mm)	16,000 lbs.	☐ SKT35035	•

*Contact the factory for stainless steel support grips.

† To determine workload safety factor, divide approximate break strength by 10. See page N-34 for strength information. Consult factory for price and availability.

Compliances, specifications and availability are subject to change without notice.

