

Commercial grade straight blade plugs & connectors

Product description


2-pole, 3-wire grounding
20A, 125V/AC
NEMA 5-20




5-20P



5-20R



4866AN



4509AN



4229

Commercial grade plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
20	125	5-20	Vinyl straight body	0.25-0.66" (6.3-16.6mm)	Y	□ 4409	□ 4228	•	•
			Vinyl angled body	0.25-0.66" (6.3-16.6mm)	Y	□ 4409AN*	—	•	•

* Not CSA cert

Commercial grade straight blade plugs & connectors

Product description

2-pole, 2-wire grounding
15A, 250V/AC
NEMA 6-15



6-15P



6-15R

Commercial grade plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
15	250	6-15	Vinyl straight body	0.25-0.66" (6.3-16.6mm)	Y	—	□ 4227	•	•
			Vinyl angled body	0.25-0.66" (6.3-16.6mm)	Y	□ 4866AN*	—	•	•

* Not CSA cert

Commercial grade straight blade plugs & connectors

Product description

2-pole, 2-wire grounding
20A, 250V/AC
NEMA 6-20



6-20P



6-20R

Commercial grade plugs & connectors



Rating A	V/AC	Vinyl NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
20	250	6-20	Vinyl straight body	0.25-0.66" (6.3-16.6mm)	Y	□ 4509	□ 4229 [†]	•	•
			Vinyl angled body	0.25-0.66" (6.3-16.6mm)	Y	□ 4509AN*	—	•	•

[†] Not NOM cert, * Not CSA cert

Color information:

Y (Yellow)



(Yellow)

Commercial grade dimensional
Information: B-15

Specification information:
Commercial grade plugs &
connectors: B-24

Compliances, specifications and availability are subject to change without notice.