

Hart lock industrial grade 15A locking devices

Product description

2-pole, 3-wire grounding
15A, 277V/AC
NEMA L7-15



L7-15R



L7-15P



4771N



CWL715C

Industrial grade plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
15	277	L7-15	Safety grip straight body	0.33-0.66" (8.4-16.7mm)	BK & W	□ CWL715P	□ CWL715C	•	•
			Auto grip straight body	0.33-0.66" (8.4-16.7mm)	BK & W	□ 4771N	□ 4772N	•	•

Industrial grade receptacles



Rating A	V/AC	NEMA	Description	Color	Single receptacle	Duplex receptacle		
15	277	L7-15	Standard industrial	BK	□ CWL715R	□ 4750	•	•

Industrial grade flanged inlets & outlets



Rating A	V/AC	NEMA	Description	Color	Flanged inlet	Flanged outlet		
15	277	L7-15	Standard industrial	BK	□ CWL715FI	—	•	•
			Standard industrial	BK & W	—	□ CWL715FO [†]	•	•

[†]Only UL Listed & CSA certified

Dimensional information:
C-76-C-78

Plug & connector specification
information:

Safety grip K7-15: C-84
Auto grip K7-15: C-84

Receptacle specification
information:

K7-15: C-86

Flanged inlet & flanged outlet
specification information:

K7-15: C-88

Color information:

BK (Black), W (White)



Compliances, specifications and availability are subject to change without notice.



Indicates NAFTA compliant - Page Q-30



RoHS compliant – Page Q-30