

# Surface Receptacles

2 Pole, 3 Wire  
15A 125V, 15A 250V  
2 Pole, 2 Wire  
15A 125V



INDUSTRIAL  
COMMERCIAL  
RESIDENTIAL

## A-18 STRAIGHT BLADE RECEPTACLES

### TESTING & CODE COMPLIANCE

- UL Listed to 498 (file no. E15058).
- Meets CSA requirements, C22.2 no. 42.
- 78: (file no. 6914 (6233-01)).
- 743: (file no. 2082 (6221-02)).

### MATERIAL CHARACTERISTICS

Temperature Rating:  
-20°C to 60°C.

## Surface Receptacles

### FEATURES

- Heavy duty plastic construction.
- For use with surface mounted wiring to expand convenience receptacles on solid plaster or concrete walls.

### 2P3W Grounding Duplex

Rating A	V	NEMA	Description	Color	Catalog No.
15	125	5-15R	For SPT Cord	Brown	78B
				Ivory	78V
15	250	6-15R	For SPT Cord	Brown	74B*
				Ivory	74V*

### 2P2W Triplex

Rating A	V	NEMA	Description	Color	Catalog No.
15	125	1-15R	For SPT Cord	Brown	743B
				Ivory	743V
15	125	1-15R	For SPT Cord	Brown	746B†
				Ivory	746V†

### 2P2W Duplex

Rating A	V	NEMA	Description	Color	Catalog No.
15	125	1-15R	For SPT Cord	Brown	79B*
				Ivory	79V*

†UL component recognized

\*Not CSA



78



743



79



1-15R



5-15R



6-15R