

## Industrial grade portable GFCIs

### Industrial grade 20A portable GFCIs

#### Product description

2-pole, 3-wire grounding  
20A, 120V/AC; 20A, 240V/AC



GF12M1NN



GF12M133

#### 20A portable GFCIs, inline series

Rating A	V/AC	NEMA	NEMA type	Connector style	Cord length	Cord gauge	Catalog no.*
20	120	N/A	4X	Flying leads - field wireable	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GF12M1NN
				Flying leads - field wireable	6' (1.83m)	12/3 AWG	<input type="checkbox"/> GF12M2NN
				Flying leads - field wireable	25' (7.62m)	12/3 AWG	<input type="checkbox"/> GF12M4NN
				Flying leads - field wireable	50' (15.24m)	12/3 AWG	<input type="checkbox"/> GF12M6NN
20	240	N/A	4X	Flying leads - field wireable	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GF12M1NN
				Flying leads - field wireable	6' (1.83m)	12/3 AWG	<input type="checkbox"/> GF12M2NN
				Flying leads - field wireable	25' (7.62m)	12/3 AWG	<input type="checkbox"/> GF12M4NN
				Flying leads - field wireable	50' (15.24m)	12/3 AWG	<input type="checkbox"/> GF12M6NN


\*Automatic reset GFCIs are also available. When ordering automatic portable GFCIs replace "M" in catalog number with "A". Example: GF12A1NN = Automatic; GF12M1NN = Manual

#### Inline series - molded plug & connector

Rating A	V/AC	NEMA	NEMA type	Connector style	Cord length	Cord gauge	Catalog no.
20	120	5-20	4X	Molded straight blade	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GF12M133
			4X	Molded locking	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GF12M144
20	240	L6-20	4X	Molded locking	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GF12M144

\*Automatic reset GFCIs are also available. When ordering automatic portable GFCIs replace "M" in catalog number with "A". Example: GF12A133 = Automatic; GF12M133 = Manual

#### Accessories for 20A portable GFCIs

Description	Catalog no.	
20A 125V/AC NEMA 5-20 watertight plug	<input type="checkbox"/> 14W33	•
20A 125V/AC NEMA 5-20 watertight connector	<input type="checkbox"/> 15W33	•
Standard depth portable outlet box with flip lids	<input type="checkbox"/> WD3059-DDN	•
20A 125V/AC NEMA 5-20 duplex straight blade receptacle - black	<input type="checkbox"/> BR20BK	•
20A 125V/AC NEMA L5-20 industrial receptacle	<input type="checkbox"/> CWL520R	•
20A 125V/AC NEMA 5-20 duplex straight blade corrosion resistant receptacle - yellow	<input type="checkbox"/> AH5362CRY	•



14W33



15W33



WD3059-DDN



BR20BK



CWL520R



AH5362CRY

## Industrial grade portable GFCIs

### Watertight portable GFCIs

#### Product description

2-pole, 3-wire grounding  
 15A, 120V/AC; 20A, 120V/AC; 20A, 240V/AC  
 30A, 120V/AC; 30A, 240V/AC



GFI12M155

#### Watertight portable GFCIs, inline series, watertight plug & connector ends



Rating A	V/AC	NEMA	NEMA type	Connector style	Cord length	Cord gauge	Catalog no.*
15	120	5-15	3R	Straight blade	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFI11M155
				Straight blade	6' (1.83m)	12/3 AWG	<input type="checkbox"/> GFI11M255
				Straight blade	25' (7.62m)	12/3 AWG	<input type="checkbox"/> GFI11M455
				Straight blade	50' (15.24m)	12/3 AWG	<input type="checkbox"/> GFI11M655
20	120	5-20	4X	Straight blade	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFI12M155
				Straight blade	6' (1.83m)	12/3 AWG	<input type="checkbox"/> GFI12M255
				Straight blade	25' (7.62m)	12/3 AWG	<input type="checkbox"/> GFI12M455
		15-20	4X	Locking	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFI12M166
				Locking	6' (1.83m)	12/3 AWG	<input type="checkbox"/> GFI12M266
				Locking	25' (7.62m)	12/3 AWG	<input type="checkbox"/> GFI12M466
20	240	L6-20	4X	Locking	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFI22M166
				Locking	6' (1.83m)	12/3 AWG	<input type="checkbox"/> GFI22M266
				Locking	25' (7.62m)	12/3 AWG	<input type="checkbox"/> GFI22M466
30	120	L5-30	4X	Locking	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFI13M166
				Locking	6' (1.83m)	12/3 AWG	<input type="checkbox"/> GFI13M266
				Locking	25' (7.62m)	12/3 AWG	<input type="checkbox"/> GFI13M466
30	240	L6-30	4X	Locking	2' (0.61m)	12/3 AWG	<input type="checkbox"/> GFI23M166
				Locking	6' (1.83m)	12/3 AWG	<input type="checkbox"/> GFI23M266
				Locking	25' (7.62m)	12/3 AWG	<input type="checkbox"/> GFI23M466

\*Automatic reset GFCIs are also available. When ordering automatic portable GFCIs replace "M" in catalog number with "A". Example: GFI12A155 = Automatic; GFI12M155 = Manual

#### Receptacles & accessories for watertight portable GFCIs

Description	Catalog no.	
20A 125V/AC NEMA 5-20 watertight single straight blade receptacle	<input type="checkbox"/> 60W33	•
20A 125V/AC NEMA 5-20 watertight duplex straight blade receptacle	<input type="checkbox"/> 60W33DPLX	•
20A 125V/AC NEMA L5-20 watertight locking receptacle	<input type="checkbox"/> L520RW	•
30A 125V/AC NEMA L5-30 watertight locking receptacle	<input type="checkbox"/> L530RW	•
20A plug closure cap	<input type="checkbox"/> 20PW	•
20A connector closure cap	<input type="checkbox"/> 20CW	•



60W33



60W33DPLX



L520RW



L530RW



20PW



20CW

**Specification information:** Specification grade 15A watertight portable GFCIs: H-18, 20A watertight portable GFCIs: H-18, 30A watertight portable GFCIs: H-18

**Compliances, specifications and availability are subject to change without notice.**



### 20A Portable GFCIs

#### Product description

2-pole, 3-wire grounding  
 20A, 120 V/AC; 20A, 208 V/AC  
 20A, 240 V/AC; 20A, 277 V/AC

#### Features

- High-strength polycarbonate housing for durability
- Compact body design
- Field wireable versions available for attachment to existing cords or equipment power supply
- Automatic and manual GFCI reset options available



GFI12M1NN



GFI12M133

#### 20A inline series - field wireable



Rating A	V/AC	NEMA TYPE†	Cord gauge	Plug type	Cord length	Catalog no.*
20	120	4X	12/3 AWG	Flying leads	2' (0.61m)	<input type="checkbox"/> GFI12M1NN
	240	4X	12/3 AWG	Flying leads	2' (0.61m)	<input type="checkbox"/> GFI22M1NN
	208	4X	12/3 AWG	Flying leads	2' (0.61m)	<input type="checkbox"/> GFI92M1NN
	120	4X	12/3 AWG	Flying leads	6' (1.83m)	<input type="checkbox"/> GFI12M2NN
	240	4X	12/3 AWG	Flying leads	6' (1.83m)	<input type="checkbox"/> GFI22M2NN
	120	4X	12/3 AWG	Flying leads	25' (7.62m)	<input type="checkbox"/> GFI12M4NN
	240	4X	12/3 AWG	Flying leads	25' (7.62m)	<input type="checkbox"/> GFI22M4NN
	120	4X	12/3 AWG	Flying leads	50' (15.24m)	<input type="checkbox"/> GFI12M6NN
	240	4X	12/3 AWG	Flying leads	50' (15.24m)	<input type="checkbox"/> GFI22M6NN

\*Automatic reset GFCIs also available. When ordering automatic portable GFCIs replace "M" in Catalog number with "A".  
 Example: GFI12A1NN = Automatic; GFI12M1NN = Manual.

#### 20A inline series - molded plug & connector



Rating A	V/AC	NEMA	Cord gauge	Plug type	Cord length	Catalog no.*
20	120	5-20	12/3 AWG	Molded straight blade	2' (0.61m)	<input type="checkbox"/> GFI12M133
	120	L5-20	12/3 AWG	Molded locking	2' (0.61m)	<input type="checkbox"/> GFI12M144
	240	L6-20	12/3 AWG	Molded locking	2' (0.61m)	<input type="checkbox"/> GFI22M144

†The housing and device must be 4X in order for the whole assembly to be 4X.

\*Automatic reset GFCIs also available. When ordering automatic portable GFCIs replace "M" in Catalog number with "A".  
 Example: GFI12A133 = Automatic; GFI12M133 = Manual.