



Powering Business Worldwide

9547DS

Coax Jack Aspire Deco Single DS

UPC: 032664646423

Brand Name: Eaton

Sub Brand: Eaton

Type: 3-Way

Special Features: Wiring Type Back and Side Wire, Power Failure Memory, Electrostatic Discharge Protection, With Preset and LED Indicator. Color White

Application: Residential

Voltage Rating: 120 Vac

Wattage: 600 W

Number Of Poles: 1

Frequency Rating: 60 Hz

Load: Incandescent, Halogen

Connection: Screw

Material: Polycarbonate

Size: 1.80 In Width X 1.52 In Depth X 4.20 In Height

Actuator: Integrated Full slide

Operating Temperature: 0 To 40 Deg C

Environmental Conditions: Indoor use

9547SG

Coax Jack Aspire Deco Single SG

UPC: 032664646430

Brand Name: Eaton

Sub Brand: Eaton

Type: 3-Way

Special Features: Wiring Type Back and Side Wire, Power Failure Memory, Electrostatic Discharge Protection, With Preset and LED Indicator. Color White

Application: Residential

Voltage Rating: 120 Vac

Wattage: 600 W

Number Of Poles: 1

Frequency Rating: 60 Hz

Load: Incandescent, Halogen

Connection: Screw

Material: Polycarbonate

Size: 1.80 In Width X 1.52 In Depth X 4.20 In Height

Actuator: Integrated Full slide

Operating Temperature: 0 To 40 Deg C

Environmental Conditions: Indoor use



Powering Business Worldwide

9547WS

Coax Jack Aspire Deco Single WS

UPC: 032664646447

Brand Name: Eaton

Sub Brand: Eaton

Type: 3-Way

Special Features: Wiring Type Back and Side Wire, Power Failure Memory, Electrostatic Discharge Protection, With Preset and LED Indicator. Color Light Almond

Application: Residential

Voltage Rating: 120 Vac

Wattage: 600 W

Number Of Poles: 1

Frequency Rating: 60 Hz

Load: Incandescent, Halogen, Magnetic Low-Voltage

Connection: Screw

Material: Polycarbonate

Size: 1.80 In Width X 1.52 In Depth X 4.20 In Height

Actuator: Integrated Full slide

Operating Temperature: 0 To 40 Deg C

Environmental Conditions: Indoor use