

Industrial grade straight blade devices

Product description


2-pole, 3-wire grounding
20A, 250V/AC
NEMA 6-20



6-20P



6-20R





5466N



5879C

Industrial grade plugs & connectors

Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
20	250	6-20	Ultra grip straight body	0.33-0.66" (8.3-16.7mm)	BK & W	□ AH5466	□ AH5469	•	•
			Quick grip straight body	0.22-0.66" (5.6-16.7mm)	Y	□ AH5464Y	□ AH5469Y	•	
			Auto grip straight body	0.33-0.66" (8.3-16.7mm)	BK & W	□ 5466N	□ 5469N	•	•

Industrial grade flanged inlets & outlets

Rating A	V/AC	NEMA	Description	Color	Inlet catalog no.	Outlet catalog no.		
20	250	6-20	Nylon construction, back wire	BK & W	□ AH5878C	□ AH5879C*	•	•

* UL Listed only

Industrial grade dimensional Information: B-14, B-15

Specification information:
Safety grip industrial plugs & connectors: B-22
Quick grip plugs & connectors: B-22
Auto grip industrial plugs & connectors: B-22
Industrial flanged inlets & flanged outlets: B-23

Color information:

BK (Black), W (White), Y (Yellow)



Compliances, specifications and availability are subject to change without notice.

 Indicates NAFTA compliant - Page Q-30

 RoHS compliant - Page Q-30