

Poles, wires	Rating	NEMA prefix	15A Straight blade		20A Straight blade	
			Receptacle, connector & flanged outlet	Plug & flanged inlet	Receptacle, connector & flanged outlet	Plug & flanged inlet
2-pole, 2-wire	125V/AC	1	4882 ◇ 	4862 ◆ 		
	125V/AC	5	AH5262C □MC AH5252 □ 6262 □D AHIG5262 □IM AH5269 ◇U 5261 △M 1547 ◇Y VGF15 □GM TRBR15 □R TRVGF15 □RGM 5262 □M AH8200 □M 8200 □HM 8210 △M IG8200 □IM TR8200 □RM VGFH15 □GM TRVGFH15 □RGM 	5269N ◇NC 5279C ◇ AH5969 ◇O WRVGF15 □ 60W47 △Y 60W47DPLX □W 15W47 ◇W 4887 ◇ BR15 □ CR15 □ IG5262 ◇O 5269NHG ◇N AH8219HG ◇U AH8119W ◇O 	AH5362 □MC AH5352 □M 6362 □DM AHIG5362 □IM 1533 ◇Y 15W33 ◇W 5361 △M VGF20 □GM TRBR20 □R TRVGF20 □RGM 5362 □M AH8300 □M 8300 □M 8310 △M IG8300 □IM TR8300 □RM VGFH20 □GM TRVGFH20 □RGM 	5369N ◇NC 5779C ◇ AH5369 ◇U WRVGF20 □ 60W33 △W 60W33DPLX □W AH5369Y ◇O 4228 ◇ BR20 □ CR20 □ IG5362 ◇O 5369NHG ◇N AH8319HG ◇U 
	250V/AC	6	AH5662 □M 5661 △ AHIG5662 □I 6662 □D 1549 ◇Y 15W49 ◇W 826 □ 816 △ 5662C □ AH8600 □M 8610 △ 	5669N ◇N 5679C ◇ AH5669 ◇U 60W49 △W 60W49DPLX □W AH5669Y ◇O 4227 ◇ 	AH5462 □M 5461 △ AHIG5462 □I 6462 □D 1548 ◇Y 15W48 ◇W 815 □ 5462C □ AH8400 □M IG8400 □I AH8225HG ◇U 	5469N ◇N 5879C ◇ AH5469 ◇L 60W48 △W 60W48DPLX □W AH5469Y ◇O 4229 ◇ 8410 △ 
	277V/AC	7	5302 □ 			7624N ◆L 
	125/250V/AC	10			805 △ 	9151N ◆L 2836 ◆ 
	125/250V/AC	14			5759 △ 	
3-pole, 3-wire	3Ø 250V/AC	15				
4-pole, 4-wire	3ØY 120/208V/AC	18				7251N ◆L 

Straight blade legend: How to use the chart

Core catalog number color indicates a device's grade:

BLACK = Industrial specification grade
BLUE = Commercial specification grade
ORANGE = Construction specification grade
GREEN = Hospital specification grade

A suffix combining a **RED** shape and alpha letter indicate a device's body, type and available options.

Device body:

- Duplex receptacle
 - △ Single receptacle
 - ◆ Plug
 - ◇ Connector
 - Flanged inlet
 - Flanged outlet
 - ◐ Hull inlet
 - Mechanical interlock
- Open shape** has holes (receptacles, connectors, outlets)
Closed shape has blades (plugs, inlets)

Device type:

- A** Angled
- D** Decorator
- G** GFCI
- H** Compact
- I** Isolated ground
- L** Safety grip
- N** Auto grip
- O** Quick grip
- R** Tamper resistant
- S** Surface
- U** Ultra grip

Device options available:

- C** Corrosion resistant
- M** ArrowLink modular
- W** Watertight
- Y** Severe duty insulated

Due to spatial constraints not all products are shown on this page. For additional product options in these configurations consult sections A, B, I, J & K.