

Plastic Body - 2/2 Normally Closed 1/8" - 1/4"

Pipe Size (in)	Orifice (in)	Cv Flow	Operating Pressure Differential (psi)				Max. Fluid Temp. °F	Valve Catalog Number	Body Material	Sealing Material	Voltage	Valve Order Code	Wattage	Approvals		Rebuild Kit Order Code	Replacement Coil Order Code	Approx. Shipping Weight (lbs.)
			Min.	Max.										UL	FM			
				Air	Water	Light Oil												
2/2 Normally Closed																		
1/8	1/8	0.30	0	125	-	-	125	USM8260101	PL	NBR	120/60INT	02823	24.9	-	-	-	186548-016-*	0.5
1/4	1/8	0.30	0	125	-	-	125	USM8260100	PL	NBR	120/60INT	00851	24.9	-	-	-	186548-016-*	0.5
	9/64	0.35	0	120	120	-	130	8260G054	PL	NBR	120/60,110/50	20937	6.1	●	-	302971	238210-032-D*	0.8
		0.35	0	120	120	-	130	8260G071	PL	NBR	120/60,110/50	20938	6.1	●	-	302971	238210-032-D*	0.8

General Service - 2/2 Normally Closed 3/8"

Pipe Size (in)	Orifice (in)	Cv Flow	Operating Pressure Differential (psi)				Max. Fluid Temp. °F	Valve Catalog Number	Body Material	Sealing Material	Voltage	Valve Order Code	Wattage	Approvals		Rebuild Kit Order Code	Replacement Coil Order Code	Approx. Shipping Weight (lbs.)
			Min.	Max.										UL	FM			
				Air	Water	Light Oil												
2/2 Normally Closed																		
3/8	1/8	0.35	0	185	180	90	180	8263H002	BR	NBR	120/60,110/50	22030	6.1	○	○	323581	238210-032-D*	1.8
		0.35	0	340	300	215	180	8263H232	BR	NBR	120/60,110/50	22040	17.1	○	○	323593	238610-132-D*	1.8
	5/32	0.52	0	210	185	100	180	8263H200	BR	NBR	120/60,110/50	22031	10.1	○	○	323593	238610-032-D*	1.8
	7/32	2.9	5	230	230	230	195	SC8238T402	BR	NBR	120/60	21899	4.0	□	-	323457	43005573	1.8
		0.73	0	125	100	100	180	8263H206	BR	NBR	120/60,110/50	22032	17.1	○	○	323593	238610-132-D*	1.8
	9/32	0.88	0	100	85	70	180	8263H210	BR	NBR	120/60,110/50	22033	17.1	○	○	323593	238610-132-D*	2.3
	5/16	1.2	5	125	125	-	180	8210B021	BR	NBR	120/60,110/50	00245	6.5	●	-	302270	216099-003-D*	1.0
		1.5	10	750	750	750	200	8223G023	BR	NYLON	120/60,110/50	20374	10.1	-	-	302313	238610-032-D*	2.9
		1.5	10	1500	1500	1500	200	8223G027	BR	NYLON	120/60,110/50	20378	17.1	-	-	302314	238610-132-D*	2.9
	3/8	1.5	5	150	125	-	180	8210G073	BR	NBR	120/60,110/50	20194	6.1	●	-	302271	238210-032-D*	2.0
		1.5	5	150	125	-	180	EF8210G073	BR	NBR	120/60,110/50	20195	6.1	●	-	302271	238214-032-D*	2.0
		1.5	5	150	125	-	180	8210G036	SS	NBR	120/60,110/50	20176	6.1	●	-	302326	238210-032-D*	2.0
		1.5	5	150	125	-	180	EF8210G036	SS	NBR	120/60,110/50	20178	6.1	●	-	302326	238214-032-D*	2.0
		1.8	0	7	5	-	180	8030G010	BR	NBR	120/60,110/50	20003	6.1	○	○	302787	238210-032-D	1.5
		1.8	0	15	-	-	180	8030G013VM	BR	NBR	120/60,110/50	20008	10.1	-	-	302788-VM	238610-032-D*	2.3
		1.8	0	15	15	-	180	8030G013	BR	NBR	120/60,110/50	20006	10.1	○	●	302788	238610-032-D*	2.3
	5/8	3	0	150	150	-	180	SC8210G093	BR	NBR	120/60,110/50	21878	10.1	-	-	302272	238612-032-*	3.2
		3	0	150	150	-	180	8210G093	BR	NBR	120/60,110/50	20221	10.1	○	-	302272	238610-032-D*	3.2
		3	0	150	150	-	180	EF8210G093	BR	NBR	120/60,110/50	20224	10.1	○	-	302272	238614-032-D*	3.2
		3	0	40	40	-	150	8210G093	BR	NBR	24/DC	20228	11.6	○	-	302372	238710-006-D*	3.2
		3	0	40	40	-	150	8210G093	BR	NBR	12/DC	20227	11.6	○	-	302372	238710-004-D*	3.2
		3	5	200	150	135	180	8210G001	BR	NBR	120/60,110/50	20032	6.1	○	-	302273	238210-032-D*	3.2
		3	5	200	150	135	180	8210G001	BR	NBR	24/60	20039	6.1	○	-	302273	238210-005-D*	3.2
		3	5	200	150	135	180	8210G001	BR	NBR	240/60,220/50	20036	6.1	○	-	302273	238210-058-D*	3.2
		3	5	200	150	135	180	EF8210G001	BR	NBR	120/60,110/50	20034	6.1	○	-	302273	238214-032-D*	3.2
		3	5	200	150	135	180	JKF8210G001	BR	NBR	120/60,110/50	20035	6.1	○	-	302273	238212-032-*	3.2
		3	5	200	150	135	180	SC8210G001	BR	NBR	120/60,110/50	21037	6.1	○	-	302273	238212-032-*	3.2
		3	5	125	100	100	150	8210G001	BR	NBR	24/DC	20041	11.6	○	-	302373	238710-006-D*	3.2
		3	5	125	100	100	150	8210G001	BR	NBR	12/DC	20040	11.6	○	-	302373	238710-004-D*	3.2
	5/8	3	5	300	300	300	175	8210G006	BR	NBR	120/60,110/50	20093	17.1	○	-	302274	238610-132-D*	3.2
		3	5	300	300	300	175	EF8210G006	BR	NBR	120/60,110/50	20094	17.1	○	-	302274	238614-132-D*	3.2
	3/4	3.4	0	50	-	-	125	8215G010	AL	NBR	120/60,110/50	20286	10.1	○	●	302350	238610-032-D*	2.8