

General Service - 2/2 Normally Open 1/8" - 2"

Pipe Size (in)	Orifice (in)	Cv Flow	Operating Pressure Differential (psi)				Max. Fluid Temp. °F	Valve Catalog Number	Body Material	Sealing Material	Voltage	Valve Order Code	Wattage	Approvals		Rebuild Kit Order Code	Replacement Coil Order Code	Approx. Shipping Weight (lbs.)	
			Min.	Max.										UL	FM				
				Air	Water	Light Oil													
2/2 Normally Open																			
1/8	1/16	0.09	0	500	300	225	180	8262G091	BR	NBR	120/60,110/50	20453	6.1	●	-	302041	238210-032-D*	2.0	
	3/32	0.15	0	275	200	150	180	8262G093	BR	NBR	120/60,110/50	20454	6.1	●	-	302041	238210-032-D*	2.6	
	1/8	0.21	0	125	100	85	180	8262G031	BR	NBR	120/60,110/50	20432	6.1	●	-	302041	238210-032-D*	2.0	
		0.21	0	125	100	85	180	8262G035	SS	NBR	120/60,110/50	20434	6.1	●	-	302043	238210-032-D*	2.6	
1/4	3/64	0.06	0	750	700	700	140	8262G260	BR	NBR	120/60,110/50	20499	10.1	●	-	302045	238610-032-D*	2.6	
	3/32	0.17	0	300	250	230	140	8262G261	BR	NBR	120/60,110/50	20500	10.1	●	-	302045	238610-032-D*	2.6	
	1/8	0.35	0	130	110	100	180	8262G262	BR	NBR	120/60,110/50	20501	10.1	●	-	302051	238610-032-D*	2.6	
		0.35	0	130	110	100	180	8262G138	SS	NBR	120/60,110/50	20456	10.1	●	-	302053	238610-032-D*	2.6	
	5/32	0.49	0	85	75	60	180	8262G263	BR	NBR	120/60,110/50	20506	10.1	●	-	302051	238610-032-D*	2.6	
	7/32	0.83	0	45	45	40	180	8262G264	BR	NBR	120/60,110/50	20509	10.1	●	-	302051	238610-032-D*	2.6	
		0.83	0	45	45	40	180	EF8262G148V	SS	FKM	120/60,110/50	20459	10.1	●	-	302055-V	238614-032-D*	2.6	
	9/32	0.96	0	30	25	20	180	8262G265	BR	NBR	120/60,110/50	20510	10.1	●	-	302051	238610-032-D*	2.6	
3/8	5/8	3	0	15	-	-	180	8210G033VH	BR	NBR	120/60,110/50	20147	10.1	-	-	302334-VH	238610-032-D*	3.4	
		3	0	150	150	125	180	8210G033	BR	NBR	120/60,110/50	20146	10.1	●	-	302334	238610-032-D*	3.4	
		3	0	150	150	125	180	EF8210G033	BR	NBR	120/60,110/50	20149	10.1	●	-	302334	238614-032-D*	3.4	
		3	0	125	125	80	150	8210G033	BR	NBR	24/DC	20153	11.6	●	-	302449	238710-006-D*	3.4	
1/2	7/16	2.2	0	15	15	-	200	8030G071	BR	NBR	120/60	21448	20.1	●	-	302798	272610-132-D*	3.4	
	5/8	3	0	150	150	100	180	8210G030	SS	NBR	120/60,110/50	20141	10.1	●	-	302347	238610-032-D*	3.4	
		3	0	150	150	100	180	EF8210G030	SS	NBR	120/60,110/50	20142	10.1	●	-	302347	238614-032-D*	3.4	
		4	0	150	150	125	180	8210G034	BR	NBR	120/60,110/50	20154	10.1	●	-	302334	238610-032-D*	3.4	
		4	0	150	150	125	180	EF8210G034	BR	NBR	120/60,110/50	20157	10.1	●	-	302334	238614-032-D*	3.4	
		4	0	150	150	125	180	SC8210G034	BR	NBR	120/60,110/50	21782	10.1	●	-	302334	238612-032-*	3.4	
		4	0	125	125	80	150	8210G034	BR	NBR	24/DC	20164	11.6	●	-	302449	238710-006-D*	3.4	
	5/8	4	5	250	200	200	180	8210G012	BR	NBR	120/60,110/50	20122	10.1	●	-	314680	238610-032-D*	3.2	
	3/4	4	0	125	-	-	125	8215G023	AL	NBR	120/60,110/50	20295	10.1	●	-	302361	238610-032-D*	2.8	
	3/4	5/8	3	0	150	150	100	180	8210G038	SS	NBR	120/60,110/50	20183	10.1	●	-	302347	238610-032-D*	3.4
3			0	150	150	100	180	EF8210G038	SS	NBR	120/60,110/50	20184	10.1	●	-	302347	238614-032-D*	3.4	
3/4		3/4	4.6	0	125	-	-	125	8215G033	AL	NBR	120/60,110/50	20303	10.1	●	-	302361	238610-032-D*	3.0
			4.6	0	125	-	-	125	EF8215G033	AL	NBR	120/60,110/50	20304	10.1	●	-	302361	238614-032-D*	3.0
			4.6	0	125	-	-	125	JKF8215G033	AL	NBR	120/60,110/50	20932	10.1	●	-	302361	238612-032-*	3.0
			5.5	0	2	2	-	180	8030G083	BR	NBR	120/60,110/50	20027	10.1	●	-	302799	238610-032-D*	3.4
			5.5	0	150	150	125	180	8210G035	BR	NBR	120/60,110/50	20166	10.1	●	-	302335	238610-032-D*	3.2
			5.5	0	150	150	125	180	EF8210G035	BR	NBR	120/60,110/50	20168	10.1	●	-	302335	238614-032-D*	3.2
			5.5	0	150	150	125	180	SC8210G035	BR	NBR	120/60,110/50	21783	10.1	●	-	302335	238612-032-*	3.2
			5.5	0	150	150	125	180	8210G035V	BR	FKM	120/60,110/50	21852	10.1	-	-	302335-V	238610-032-D*	3.2
5.5		0	125	125	80	150	8210G035	BR	NBR	24/DC	20175	11.6	●	-	302450	238710-006-D*	3.2		
6.5		5	250	200	200	180	8210G013	BR	NBR	120/60	21606	16.1	●	-	302336	272610-032-D*	4.0		
1	1	13	5	125	125	125	180	8210D014	BR	NBR	24/DC	21849	16.8	●	-	302338	097617-005-D*	5.0	
		13	0	125	125	125	180	8210B057	BR	NBR	120/60,110/50	00272	20	●	-	302337	099257-005-D*	6.5	
		13	5	150	150	125	180	8210G014	BR	NBR	120/60	21419	16.1	●	-	302338	272610-032-D*	5.0	
		13	5	150	150	125	180	EF8210G014	BR	NBR	120/60	21741	16.1	●	-	302338	272614-032-D*	5.0	
	1 5/8	22	0	25	-	-	125	8215C053	AL	NBR	120/60,110/50	00617	15.4	●	-	304691	099257-001-D*	1.3	
		22	0	25	-	-	104	EF8215C053	AL	NBR	120/60,110/50	20308	15.4	●	-	304695	099257-001-D*	1.3	
1 1/4	1 1/8	15	5	150	150	125	180	8210G018	BR	NBR	120/60	21720	16.1	●	-	302338	272610-032-D*	6.0	
	1 5/8	33	0	25	-	-	125	8215C063	AL	NBR	120/60,110/50	00619	15.4	●	-	304691	099257-001-D*	3.3	
1 1/2	1 1/4	22.5	0	125	125	125	180	8210B059	BR	NBR	120/60,110/50	00275	20	●	-	302340	099257-005-D*	8.5	
		22.5	5	150	150	125	180	8210G032	BR	NBR	120/60	21721	16.1	●	-	302341	272610-032-D*	8.0	
	1 5/8	37	0	25	-	-	125	8215C073	AL	NBR	120/60,110/50	00623	15.4	●	-	304691	099257-001-D*	3.3	
2	1 3/4	43	5	125	125	125	180	8210G103	BR	NBR	120/60	21724	16.1	●	-	304361	272610-032-D*	12.0	
		43	5	125	125	125	180	EF8210G103	BR	NBR	120/60	21586	16.1	●	-	304361	272614-032-D*	12.0	
	2 2/32	58	0	25	-	-	125	8215C083	AL	NBR	120/60,110/50	00625	15.4	●	-	304692	099257-001-D*	5.3	