

DuraShield | Opaque Cover | W

FLUSH FITTING COVER FASTENED BY CAPTIVE LID SCREWS



CONSTRUCTION

Material (Box & Cover)	Hot Compression Molded Fiberglass Reinforced Polyester (Thermoset)
Gasket Material	Poured polyurethane seamless gasket
Cover Screw Material	304 Stainless Steel
Cover Screw Size	M6 x 35 mm
Cover Screw Torque	17-22 in.-lbs.
Mounting Bosses	Panel mounting capability for fixed rear panel
Metal Inserts	All bosses utilize threaded brass inserts accepting M6 screws
Soft Edge Design	Rounded Edges, Minimal Protrusions Or Exposed Pocket Areas

INDUSTRY STANDARDS

UL/cUL File #	E64358
NEMA Ratings	1, 3, 3S, 4X, 6, 6P, 12
(UL508A, UL50 & UL50e)	
CSA Std. C22.2 File #	LR069014
IEC 60529 Ratings	IP66, IP67, IP68
Temperature Range	(-26°F to +257°F) (-32°C to +125°C)
Flammability Rating	UL94-V0
Self Extinguishing	Non-halogenated, Non-flame propagating
Certifications	UL, CSA, CE, REACH, RoHS
Outdoor UV Exposure (UL 746C)	(f1) Rated
Chemical Resistance	See chart on page 120

ACCESSORIES

BACK PANELS

Aluminum	BPDU__A	pg. 109
-----------------	---------	---------

ACCESSORIES


4X Breather Vent	pg. 102
4X Drain Vent	pg. 102
PluggIt	pg. 103
Mounting Feet	pg. 113
Thermal Accessories	pg. 115
All Other Accessories	Pg. 102-117

MODIFICATIONS

Custom Colors	pg. 10-11
Silk Screening	pg. 10-11
Custom Cutouts/Holes	pg. 10-11

DuraShield | Opaque Cover | W

TECHNICAL DRAWINGS / DIMENSIONS



DURASHIELD W DIMENSIONS

SIZE ID NUMBER	OVERALL H X W X D	INSIDE A X B X C	MOUNTING E X F	J	K	L	M	N	P	SHIPPING WEIGHT	PANEL NUMBER
DU333W	2.95 x 3.15 x 2.78 (75 x 80 x 76)	2.56 x 2.76 x 2.56 (65 x 70 x 65)	1.57 x 2.48 (40 x 63)	2.26 (57)	N/A	2.28 (58)	1.06 (27)	1.93 (49)	N/A	0.81 LB	BPDU33A*
DU342W	2.95 x 4.33 x 2.22 (75 x 110 x 56)	2.56 x 3.93 x 1.81 (65 x 100 x 46)	1.77 x 3.86 (45 x 98)	1.53 (39)	N/A	3.50 (89)	1.29 (33)	3.37 (86)	N/A	.88 LB	BPDU34A*
DU554W	4.72 x 4.80 x 3.58 (120 x 122 x 91)	4.33 x 4.41 x 3.15 (110 x 112 x 80)	3.23 x 4.17 (82 x 106)	2.93 (74)	2.05 (52)	3.74 (95)	2.56 (65)	3.50 (89)	1.02 (26)	1.7 LB	BPDU55A*
DU593W	4.72 x 8.66 x 3.19 (120 x 220 x 81)	4.34 x 8.28 x 2.83 (110 x 210 x 72)	3.23 x 8.03 (82 x 204)	2.62 (67)	2.05 (52)	7.60 (193)	2.57 (65)	7.37 (187)	1.02 (26)	2.4 LB	BPDU59A*
DU594W	4.72 x 8.66 x 3.58 (120 x 220 x 91)	4.33 x 8.27 x 3.15 (110 x 210 x 80)	3.23 x 8.03 (82 x 204)	2.93 (74)	2.05 (52)	7.60 (193)	2.57 (65)	7.37 (187)	1.02 (26)	2.5 LB	BPDU59A*
DU774W	6.30 x 6.30 x 3.58 (160 x 160 x 91)	5.79 x 5.79 x 3.11 (147 x 147 x 79)	4.33 x 5.51 (110 x 140)	2.93 (74)	2.99 (76)	5.20 (132)	3.50 (89)	4.68 (119)	1.50 (38)	2.8 LB	BPDU77A*
DU7114W	6.30 x 10.24 x 3.58 (160 x 260 x 91)	5.79 x 9.72 x 3.11 (147 x 247 x 79)	4.33 x 9.45 (110 x 240)	2.93 (74)	2.99 (76)	9.13 (232)	3.50 (89)	8.62 (219)	1.50 (38)	3.8 LB	BPDU711A*
DU10105W	9.84 x 10.04 x 4.76 (250 x 255 x 121)	9.31 x 9.51 x 4.29 (236 x 242 x 109)	7.87 x 9.25 (200 x 235)	4.11 (104)	3.94 (100)	8.94 (227)	7.03 (179)	8.41 (214)	1.97 (50)	6.4 LB	BPDU1010A*
DU10165W	9.84 x 15.75 x 4.76 (250 x 400 x 121)	9.31 x 15.22 x 4.29 (236 x 387 x 109)	7.87 x 14.96 (200 x 380)	4.09 (104)	3.94 (100)	14.65 (327)	7.03 (179)	14.12 (359)	1.97 (50)	8.8 LB	BPDU1016A*
DU14144W	14.17 x 14.17 x 3.58 (360 x 360 x 91)	13.66 x 13.66 x 3.11 (347 x 347 x 79)	12.20 x 13.39 (310 x 340)	2.91 (74)	5.35 (136)	13.07 (332)	11.38 (289)	12.56 (319)	2.68 (68)	8.0 LB	BPDU1414A*
DU16165W	15.94 x 15.75 x 4.76 (405 x 400 x 121)	15.42 x 15.22 x 4.29 (392 x 387 x 109)	13.98 x 14.96 (355 x 380)	4.09 (104)	9.84 (250)	14.65 (372)	13.14 (334)	14.12 (359)	4.92 (125)	11.0 LB	BPDU1616A*

* Panel ordered separately