

Single and Three Phase, Totally Enclosed

Hp	RPM	NEMA Frame	Encl.	Catalog Number	List Price	Mult. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	EISA Status (a)	Notes (a)
1 1/2	3600	56C	TENV	CEWDM3550	941	WD	12.07	44	85.5	208-230/460	2	C	1, 60
		56C	TENV	CWDM3550	689	WD	12.94	51	82.5	208-230/460	2.1	C	1, 60
	1800	56C	TEFC	CWDM3554	705	WD	12.24	34	78.5	208-230/460	2.5	C	1
		145TC	TENV	CEWDM3554T	983	WD	13.00	48	86.5	230/460	2	C	1, 30, 60
		145TC	TENV	CWDM3554T	725	WD	12.12	42	85.5	208-230/460	2.3	C	1, 60
1200	56C	TEFC	CWDM3557	899	WD	13.24	39	75.5	230/460	2.5	C	1	
2	3600	56HCY	TEFC	CEWDM3555	1,018	WD	14.12	51	85.5	208-230/460	2.5	C	1
		56HCY	TEFC	CWDM3555	780	WD	13.59	40	80	208-230/460	2.8	C	1
		145TC	TEFC	CEWDM3555T	1,038	WD	14.17	51	85.5	208-230/460	2.5	A	1
		145TC	TEFC	CWDM3555T	800	WD	13.30	44	84	208-230/460	2.6	D	1
	1800	56C	TEFC	CWDM3558	778	WD	13.24	42	82.5	208-230/460	3.1	C	1
		145TC	TEFC	CEWDM3558T	1,083	WD	14.16	47	86.5	208-230/460	2.7	A	1
	1200	145TC	TEFC	CWDM3558T	812	WD	13.30	41	84	208-230/460	3.1	D	1
		184TC	TEFC	CEWDM3614T	1,270	WD	18.05	79	88.5	208-230/460	3.3	A	
		184TC	TEFC	CWDM3614T	1,075	WD	16.54	75	86.5	208-230/460	3.5	D	1
3	3600	145TC	TEFC	CEWDM3559T	1,279	WD	15.55	59	86.5	230/460	3.6	A	1, 30
		145TC	TEFC	CWDM3559T	957	WD	14.17	55	85.5	208-230/460	3.7	D	1
		182TC	TEFC	CEWDM3610T	1,206	WD	15.18	67	86.5	230/460	3.7	A	1
		182TC	TEFC	CWDM3610T	1,056	WD	15.18	57	85.5	208-230/460	3.7	D	1
	1800	182TC	TEFC	CEWDM3611T	1,423	WD	16.54	75	89.5	208-230/460	4.1	A	1
		182TC	TEFC	CWDM3611T	1,066	WD	16.54	74	87.5	208-230/460	4.1	D	1
1200	213TC	TEFC	CEWDM3704T	1,674	WD	19.76	130	89.5	230/460	4.6	A	1	
	213TC	TEFC	CWDM3704T	1,354	WD	18.65	112	87.5	208-230/460	4.6	D	1	
5	3600	184TC	TEFC	CEWDM3613T	1,693	WD	16.54	84	88.5	208-230/460	5.6	A	1
		184TC	TEFC	CWDM3613T	1,335	WD	16.54	74	87.5	208-230/460	5.8	D	1
	1800	184TC	TEFC	CEWDM3615T	1,612	WD	18.04	96	89.5	230/460	6.5	A	1, 30
		184TC	TEFC	CWDM3615T	1,205	WD	16.54	82	87.5	208-230/460	7.1	D	1
	1200	215TC	TEFC	CEWDM3708T	1,983	WD	20.51	142	89.5	230/460	7.2	A	1, 30
		215TC	TEFC	CWDM3708T	1,737	WD	19.78	132	87.5	208-230/460	7.5	D	1
7 1/2	3600	184TC	TEFC	CEWDM3616T	2,012	WD	18.04	99	89.5	208-230/460	8.4	A	1
		184TC	TEFC	CWDM3616T	1,523	WD	18.04	89	88.5	208-230/460	8.7	D	1
		213TC	TEFC	CEWDM3709T	2,385	WD	19.78	139	89.5	208-230/460	8.6	A	1
		213TC	TEFC	CWDM3709T	1,656	WD	18.54	101	88.5	208-230/460	8.7	D	1
	1800	213TC	TEFC	CEWDM3710T	2,040	WD	19.78	129	91.7	230/460	9.4	A	1, 30
		213TC	TEFC	CWDM3710T	1,528	WD	18.65	131	89.5	208-230/460	10.1	D	1
1200	254TC	TEFC	CEWDM22976T	3,404	WD	23.57	247	91	230/460	10.7	A	1, 30	
	254TC	TEFC	CWDM22976T	2,781	WD	23.57	213	89.5	208-230/460	11.2	D	1	
10	3600	215TC	TEFC	CEWDM3711T	2,625	WD	19.78	151	90.2	230/460	11.2	A	1, 30
		215TC	TEFC	CWDM3711T	1,964	WD	18.65	128	89.5	208-230/460	11.5	D	1
	1800	215TC	TEFC	CEWDM3714T	2,319	WD	21.27	158	91.7	230/460	12.5	A	1
		215TC	TEFC	CWDM3714T	1,735	WD	19.78	134	89.5	208-230/460	13.5	D	1
	1200	256TC	TEFC	CEWDM23932T	3,870	WD	23.57	280	91	230/460	14.4	A	1, 30
		256TC	TEFC	CWDM23932T	3,129	WD	23.57	245	89.5	208-230/460	15.3	D	1
15	3600	215TC	TEFC	CEWDM3713T	3,298	WD	21.26	174	91	230/460	16.6	A	1
		215TC	TEFC	CWDM3713T	2,468	WD	21.26	169	90.2	208-230/460	17	D	1
		254TC	TEFC	CEWDM23994T	4,633	WD	21.94	158	91	230/460	16.6	A	1
		254TC	TEFC	CWDM23994T	3,440	WD	21.94	195	90.2	208-230/460	17	D	1
	1800	254TC	TEFC	CEWDM23933T	4,560	WD	23.57	226	92.4	230/460	18	A	1
254TC		TEFC	CWDM23933T	3,386	WD	23.57	248	91	230/460	17.3	D	1, 30	
20	3600	256TC	TEFC	CEWDM41906T	5,318	WD	23.57	242	91	230/460	22.5	A	1
		256TC	TEFC	CWDM41906T	3,950	WD	23.57	274	91	230/460	22.7	D	1, 30
	1800	256TC	TEFC	CEWDM23934T	5,289	WD	23.57	280	93	208-230/460	24	A	1
		256TC	TEFC	CWDM23934T	3,929	WD	23.57	282	91.7	230/460	23	D	1, 30

(a) See notes on inside back flap.

General Information

Premium Efficient Super-E® Motors

Single Phase Motors

General Purpose Industrial Motors

Severe Duty Motors

Washdown Duty Motors

Explosion Proof Motors

Pump Motors

Light Industrial/Commercial Motors

HVAC Motors