

BALDOR • RELIANCE®**Premium Efficient Super-E® Motors****Stainless Steel,
Three Phase,
Totally Enclosed,
C-Face,
Foot Mounted****1 thru 20 Hp****NEMA 143TC thru 256TC****Applications:** Food processing, packaging, outdoor and highly corrosive environments.**Features:** All external surfaces 300 series stainless steel: motor frame, endplates, conduit box, shaft and base. Moisture resistant insulation system. Four condensate drains in each endplate. Endplate rabbets sealed and conduit box gasketed. Labyrinth seals each end. Especially effective in highly corrosive environments where paint or other finishes do not hold up. Super-E® motors have NEMA Premium® efficiency and 3 year warranty.

Hp	RPM	NEMA Frame	Catalog Number	List Price	Mult. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	EISA Status (a)	Notes (a)
1	1800	143TC	CESSWDM3546T	1,257	WD	11.09	42	87.5	208-230/460	1.5	C	
		143TC	CESSWDM3546T-5	1,257	WD	11.09	42	87.5	575	1.1	C	
1 1/2	3600	143TC	CESSWDM3550T	1,261	WD	13.23	50	85.5	208-230/460	1.8	C	
		145TC	CESSWDM3554T	1,281	WD	13.42	45	87.5	208-230/460	2.1	A	
	1800	145TC	CESSWDM3554T-5	1,281	WD	13.42	45	87.5	575	1.6	A	
		145TC	CESSWDM3555T	1,529	WD	14.30	55	86.5	230/460	2.5	A	
2	1800	145TC	CESSWDM3558T	1,539	WD	15.67	62	88.5	208-230/460	2.8	A	
		145TC	CESSWDM3558T-5	1,539	WD	15.67	62	88.5	575	2.2	A	
		145TC	CESSWDM3559T	1,842	WD	15.67	44	86.5	208-230/460	3.7	A	
3	3600	182TC	CESSWDM3610T	1,967	WD	16.82	82	88.5	208-230/460	3.7	A	
		1800	CESSWDM3611T	1,799	WD	16.82	94	89.5	230/460	4	A	1
		3600	CESSWDM3613T	2,093	WD	18.32	107	90.2	230/460	5.7	A	1
5	1800	184TC	CESSWDM3615T	2,025	WD	18.32	115	90.2	230/460	6.4	A	1, 30
		3600	CESSWDM3709T	2,456	WD	19.03	164	91	230/460	8.3	A	1
7 1/2	1800	213TC	CESSWDM3710T	2,533	WD	20.16	157	91.7	230/460	9.5	A	1
		3600	CESSWDM3711T	2,741	WD	20.16	185	91.7	208-230/460	10.6	A	1
10	1800	215TC	CESSWDM3714T	2,794	WD	21.66	190	92.4	230/460	12.5	A	1
		3600	CESSWDM23994T	5,595	WD	24.67	240	91	208-230/460	16.5	A	1
15	1800	254TC	CESSWDM23933T	5,506	WD	24.67	246	92.4	230/460	17.5	A	1, 30
		3600	CESSWDM41906T	6,422	WD	24.67	292	91	230/460	21.5	A	1
20	1800	256TC	CESSWDM23934T	6,386	WD	24.67	300	93	230/460	23.4	A	1, 30

(a) See notes on inside back flap.