

IEEE 841, Three Phase, Totally Enclosed, 460 Volts

Hp	RPM	NEMA Frame	Enclosure	Catalog Number	List Price	Mult. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
50	3600	326TS	TEFC	EC P84114T-4	7,821	SD	29.16	623	93	460	55	1
	1800	326T	TEFC	EC P84115T-4	7,783	SD	30.66	679	94.5	460	57	1
	1200	365T	TEFC	EC P84312T-4	11,355	SD	33.49	928	94.1	460	61.7	1
60	3600	364TS	TEFC	EC P84310T-4	11,558	SD	31.37	905	95	460	65.1	1
	1800	364T	TEFC	EC P84314T-4	10,335	SD	33.49	913	95	460	68	1
	1200	404T	TEFC	EC P84403T-4	14,718	SD	38.32	1271	95	460	69	1
75	3600	365TS	TEFC	EC P84313T-4	12,802	SD	31.37	1045	94.5	460	80.7	1
	1800	365T	TEFC	EC P84316T-4	12,019	SD	33.49	971	95.4	460	85.9	1
	1200	405T	TEFC	EC P84404T-4	17,827	SD	38.20	1327	94.5	460	86.8	1
100	3600	405TS	TEFC	EC P84402T-4	15,341	SD	35.19	1330	95	460	110	1
	1800	405T	TEFC	EC P84400T-4	16,043	SD	38.32	1299	95.4	460	112	1
	1200	444T	TEFC	EC P84409T-4	19,609	SD	44.75	1940	95	460	119	1
		444T	TEFC	EC P84909T-4	19,609	SD	44.75	1933	95	460	119	1, 99
125	3600	444TS	TEFC	EC P84412T-4	17,941	SD	40.98	1968	95	460	137	1
		444TS	TEFC	EC P84412T-4E	17,941	SD	40.88	1679	95.4	460	137	1, 56
		444TS	TEFC	EC P84912T-4	17,941	SD	40.98	1968	95	460	137	1, 99
	1800	444T	TEFC	EC P84410T-4	18,198	SD	44.75	2020	95.4	460	144	1
		444T	TEFC	EC P84410T-4E	18,198	SD	44.62	1746	95.8	460	139	1, 56
		444T	TEFC	EC P84910T-4	18,198	SD	44.75	1779	95.4	460	144	1, 99
	1200	445T	TEFC	EC P84411T-4	22,257	SD	44.75	2083	95	460	146	1
150	3600	445TS	TEFC	EC P84413T-4	20,617	SD	40.98	2053	95	460	164	1
		445TS	TEFC	EC P84413T-4E	20,617	SD	40.88	1910	96.2	460	164	1, 56
		445TS	TEFC	EC P84913T-4	20,617	SD	40.98	2049	95	460	164	1, 99
	1800	445T	TEFC	EC P84406T-4	21,521	SD	44.75	2184	95.8	460	169	1
		445T	TEFC	EC P84906T-4	21,521	SD	44.75	2175	95.8	460	169	1, 99
		447T	TEFC	EC P844156T-4	24,739	SD	48.24	2536	95.8	460	170	1
	1200	447T	TEFC	EC P844156T-4	25,964	SD	48.24	2615	95.8	460	170	1, 5
		447T	TEFC	EC P849156T-4	24,739	SD	48.24	2598	95.8	460	170	1, 99
		447T	TEFC	EC P849156T-4	25,964	SD	48.24	2615	95.8	460	170	1, 5, 99
200	3600	447TS	TEFC	EC P84416T-4	27,256	SD	44.48	2433	96.2	460	213	1
		447T	TEFC	EC P84407T-4	25,892	SD	48.24	2582	96.2	460	223	1
	1800	447T	TEFC	EC P84407TR-4	27,119	SD	48.24	2676	96.2	460	223	1, 5
		449T	TEFC	EC P844206T-4	32,865	SD	53.24	3125	95.8	460	225	1
		449T	TEFC	EC P844206T-4	34,092	SD	53.24	3108	95.8	460	225	1, 5
		449T	TEFC	EC P849206T-4	32,865	SD	53.24	3085	95.8	460	225	1, 99
		449T	TEFC	EC P849206T-4	34,092	SD	53.24	3108	95.8	460	225	1, 5, 99
250	3600	449TS	TEFC	EC P844252T-4	43,915	SD	49.48	2790	96.2	460	266	1
		449TS	TEFC	EC P849252T-4	43,915	SD	49.48	2798	96.2	460	266	1, 99
	1800	449T	TEFC	EC P84408T-4	33,052	SD	53.24	2959	96.2	460	276	1
		449T	TEFC	EC P84408TR-4	34,246	SD	53.24	2995	96.2	460	276	1, 5
		449T	TEFC	EC P84908T-4	33,052	SD	53.24	2971	96.2	460	276	1, 99
		449T	TEFC	EC P84908TR-4	34,246	SD	53.24	2995	96.2	460	276	1, 5, 99
		1200	449T	TEFC	EC P844256T-4	46,128	SD	53.24	3125	95.8	460	287
C-Face, Foot Mounted												
1	3600	143TC	TEFC	CE CP83580T-4	1,087	SD	13.38	63	84	460	1.4	1
		143TC	TENV	CEN CP83580T-4	1,039	SD	12.00	61	84	460	1.3	1
	1800	143TC	TEFC	CE CP83581T-4	1,190	SD	13.38	71	87.5	460	1.5	1
		143TC	TENV	CEN CP83581T-4	1,130	SD	12.00	64	87.5	460	1.5	1
1 1/2	1200	145TC	TEFC	CE P83582T-4	1,273	SD	13.38	69	82.5	460	1.7	1
	3600	143TC	TEFC	CE CP83583T-4	1,164	SD	13.38	71	85.5	460	2	1
	1800	145TC	TEFC	CE CP83584T-4	1,212	SD	13.38	75	88.5	460	2.1	1
2	1200	182TC	TEFC	CE P83667T-4	1,461	SD	16.69	108	87.5	460	2.5	1
	3600	145TC	TEFC	CE CP83586T-4	1,277	SD	13.38	80	86.5	460	2.4	1
	1800	145TC	TEFC	CE CP83587T-4	1,262	SD	13.38	78	88.5	460	2.8	1
	1200	184TC	TEFC	CE CP83664T-4	1,681	SD	16.69	120	88.5	460	3.2	1

(a) See notes on inside back flap.

All ratings are 1.15 service factor at 40°C ambient.

All ratings meet the intent of IEEE-45 for weather protection, and are suitable for use in a 50°C ambient with a 1.0 service factor.

Cast Iron Frame

Red Catalog Number indicates **NEW** Product.