

BALDOR • RELIANCE**Premium Efficient Super-E® Motors****575 Volt,
Three Phase,
ODP, Foot Mounted****1 thru 150 Hp****NEMA 143T thru 444T****Applications:** Pumps, compressors, fans, conveyors, machine tools and other applications where 575 volt three phase power is available.**Features:** Ball bearings. Mount in any position. Heavy-gauge steel and cast iron frames. Super-E® motors have NEMA Premium® efficiency and 3 year warranty.

Hp	RPM	NEMA Frame	Catalog Number	List Price	Mult. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	EISA Status ^(a)	Notes ^(a)
1	1800	143T	EM3116T-5	628	LS	11.12	33	85.5	575	1.1	A	1
1 1/2	1800	145T	EM3154T-5	656	LS	12.12	40	86.5	575	1.7	A	1
2	1800	145T	EM3157T-5	703	LS	13.00	46	86.5	575	2.1	A	1
3	1800	182T	EM3211T-5	758	LS	15.00	66	89.5	575	3.1	A	1
5	1800	184T	EM3218T-5	830	LS	15.00	74	89.5	575	5.2	A	1
7 1/2	1800	213T	EM3311T-5	1,220	LS	16.32	114	91	575	7.6	A	1
10	1800	215T	EM3313T-5	1,477	LS	17.45	145	91.7	575	10	A	1
15	1800	254T	EM2513T-5	2,091	LS	21.69	234	93	575	14.1	A	1
20	1800	256T	EM2515T-5	2,290	L1	21.69	237	93	575	18.9	A	1
25	1800	284T	EM2531T-5	2,791	L1	23.81	330	93.6	575	24.2	A	1
30	1800	286T	EM2535T-5	3,052	L1	25.06	356	94.1	575	28	A	1
40	1800	324T	EM2539T-5	3,982	L1	26.69	482	94.1	575	37.4	A	1
50	1800	326T	EM2543T-5	4,394	L1	27.69	445	94.5	575	46	A	1
60	1800	364T	EM2547T-5	5,532	L1	30.69	726	95	575	56	A	1
75	1800	365T	EM2551T-5	6,790	L1	33.72	808	95	575	69	A	1
100	1800	404T	EM2555T-5	7,900	L1	36.97	898	95.4	575	92	A	1
125	1800	405T	EM2559T-5	9,691	L1	34.47	1238	95.4	575	115	A	1
150	1800	444T	EM2558T-5	10,765	L1	39.56	1405	95.8	575	136	A	1

^(a) See notes on inside back flap.**MEETS NRC CANADIAN STANDARDS FOR EFFICIENCY.**