

**200 Volt,
Three Phase,
ODP, Foot Mounted**
1 thru 100 Hp
NEMA 143T thru 404T

Applications: Pumps, fans, compressors, blowers, machine tools, conveyors and many other applications requiring 200 volt power.



Features: 1.15 Service Factor, positively locked drive end bearing on 254T and larger, ball bearings, dynamically balanced rotors. Super-E motors have NEMA Premium® efficiency and 3 year warranty.

Hp	RPM	NEMA Frame	Catalog Number	List Price	Mult. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	EISA Status (a)	Notes (a)
F1 Mounting												
1	1800	143T	EM3116T-8	561	L1	11.12	36	85.5	200	3.2	B	1, 68
1 1/2	1800	145T	EM3154T-8	586	L1	12.12	42	86.5	200	4.8	B	1, 68
2	1800	145T	EM3157T-8	629	L1	13.00	47	86.5	200	6.1	B	1, 68
3	1800	182T	EM3211T-8	678	L1	15.00	68	89.5	200	9.3	B	1, 68
5	1800	184T	EM3218T-8	742	L1	15.00	72	89.5	200	15	B	1, 68
7 1/2	1800	213T	EM3311T-8	1,090	L1	16.32	116	91	200	22.4	B	1, 68
10	1800	215T	EM3313T-8	1,319	L1	17.45	148	91.7	200	29.5	B	1, 68
15	1800	254T	EM2513T-8	1,869	L1	21.69	234	93	200	40.7	B	1, 68
20	3600	254T	EM2514T-8	2,172	L1	21.69	186	91	200	52.3	B	1, 24, 69
	1800	256T	EM2515T-8	2,346	L1	21.69	237	93	200	54.3	B	1, 24, 69
25	3600	256T	EM2516T-8	2,607	L1	21.69	242	91.7	200	63.2	B	1, 24, 69
	1800	284T	EM2531T-8	2,860	L1	23.81	313	93.6	200	69.5	B	1, 24, 69
30	1800	286T	EM2535T-8	3,128	L1	25.06	353	94.1	200	81	B	1, 24, 69
40	3600	286TS	EM2538T-8	3,963	L1	23.69	377	92.4	200	105	B	1, 24, 69
	1800	324T	EM2539T-8	4,081	L1	26.69	488	94.1	200	107	B	1, 24, 69
50	1800	326T	EM2543T-8	4,503	L1	27.69	521	94.5	200	132	B	1, 24, 69
60	1800	364T	EM2547T-8	5,670	L1	30.69	615	95	200	160	B	1, 24, 69
75	1800	365T	EM2551T-8	6,959	L1	29.69	808	95	200	195	B	1, 24, 69
100	1800	404T	EM2555T-8	8,097	L1	36.97	1114	95.4	200	263	B	1, 24, 69
F2 Mounting												
2	1800	145T	EFM3157T-8	629	L1	13.00	48	86.5	200	6.1	B	1, 68
3	1800	182T	EFM3211T-8	678	L1	15.00	66	89.5	200	9.3	B	1, 68
5	1800	184T	EFM3218T-8	742	L1	15.00	69	89.5	200	15	B	1, 68
7 1/2	1800	213T	EFM3311T-8	1,090	L1	16.32	109	91	200	22.3	B	1, 68
10	1800	215T	EFM3313T-8	1,319	L1	17.45	127	91.7	200	29.5	B	1, 68
15	1800	254T	EFM2513T-8	1,869	L1	21.69	234	93	200	40.7	B	1, 68
20	1800	256T	EFM2515T-8	2,346	L1	21.69	237	93	200	54.3	B	1, 24, 69

(a) See notes on inside back flap.

Custom TEFC motors available through 2,250 Hp; Open and WPIL custom motors through 15,000 Hp. Contact your Baldor•Reliance Sales Representative.

■ Cast Iron Frame