

BALDOR • RELIANCE**Farm Duty Motors****Grain Dryer/
Centrifugal Fan,
Single and
Three Phase,
TEFC and ODP****5 thru 50 Hp****NEMA 184TZ thru 326TZ****Applications:** High pressure grain drying and storage for commercial and farm applications.**Features:** Shaft length is 1" longer than NEMA standard. Screens to protect against entry of trash, snakes and rodents. Three phase ratings meet EPA efficiency standards.

Hp	RPM	NEMA Frame	Catalog Number	List Price	Mult. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	EISA Status ^(a)	Notes ^(a)
Single Phase, Open Drip Proof												
5	1800	184TZ	GDL1605T	1,431	L1	19.06	98	80	230	22.5	C	2, 20
7 1/2	1800	215TZ	GDL1607T	1,882	L1	22.57	161	82.5	230	32	C	1
10	1800	215TZ	GDL1610T	2,178	L1	22.85	164	84	230	40	C	2, 20
16	1800	256TZ	GDL1615T	3,240	L1	24.19	288	86.5	208-230	62	C	2, 20
Three Phase, Open Drip Proof												
5	1800	184TZ	GDM3218T	791	L1	16.00	69	87.5	208-230/460	6.9	C	
7 1/2	1800	213TZ	GDM3311T	1,123	L1	18.00	92	88.5	208-230/460	10	C	
10	1800	215TZ	GDM3313T	1,361	L1	17.32	129	89.5	208-230/460	13.4	C	
15	1800	254TZ	GDM2513T	1,675	L1	21.00	172	91	208-230/460	19	C	1
20	1800	254TZ	GDM2515T	2,206	L1	23.25	165	91.7	230/460	24	C	30
25	1800	284TZ	GDM2531T	2,710	L1	24.44	329	91.7	230/460	31	C	30
30	1800	284TZ	GDM2535T	3,152	L1	25.94	351	92.4	230/460	36	C	30
Three Phase, Totally Enclosed Fan Cooled												
3	1800	182TZ	GDM3611T	793	L1	16.14	59	84	208-230/460	4.1	C	1
5	1800	184TZ	GDM3615T	918	L1	17.55	77	85.5	208-230/460	6.6	C	1
7 1/2	1800	213TZ	GDM3710T	1,169	L1	18.90	115	89.5	208-230/460	10.1	C	1
10	1800	215TZ	GDM3714T	1,886	L1	20.03	139	89.5	208-230/460	13.5	C	1
15	1800	254TZ	GDM2333T	2,493	L1	22.07	231	89.5	208-230/460	18.9	C	1
20	1800	256TZ	GDM2334T	2,669	L1	23.83	322	91	230/460	25	C	1, 30
25	1800	284TZ	GDM4103T	3,798	L1	26.93	322	92.4	230/460	29	C	1, 30
30	1800	286TZ	GDM4104T	4,485	L1	26.93	322	92.4	230/460	36	C	1, 30
40	1800	324TZ	GDM4110T	5,956	L1	31.39	485	93	230/460	47	C	1
50	1800	326TZ	GDM4115T	6,169	L1	31.28	552	91	230/460	60	C	1, 30

^(a) See notes on inside back flap.

■ Cast Iron Frame