

**U-Frame,  
Single Phase**

**1 thru 5 Hp**

**NEMA 182 thru 215**

**Applications:** Pumps, compressors, fans, conveyors, machine tools and other general purpose single phase applications requiring NEMA U-frame mounting.

**Features:** Ball bearings, heavy-gauge steel frames, Exxon Polyrex EM grease, All the features of our stock general purpose single phase NEMA T-frame motors but with NEMA U-frame mounting dimensions.



Hp	RPM	NEMA Frame	Catalog Number	List Price	Mult. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
<b>Totally Enclosed, Foot Mounted</b>											
1	1800	182	<b>L3601</b>	996	L1	14.31	55	72	115/230	6	3, 30
	1200	184	<b>L3607</b>	1,590	L1	15.69	74	67	115/230	7	3, 30
1 1/2	1800	184	<b>L3603</b>	1,085	L1	15.69	66	70	115/230	9.5	3, 30
2	1800	184	<b>L3605</b>	1,214	L1	15.69	67	75.5	115/230	11.5	3, 30
		184	<b>L3605M</b>	1,301	L1	15.69	66	75.5	115/230	11.5	3, 30
	1200	215	<b>L3703</b>	2,626	L1	17.51	113	80	115/230	9.4	2, 30, 65
	1800	215	<b>L3705</b>	2,070	L1	17.51	117	80	115/230	14	30, 65
3	1200	215	<b>L3706</b>	3,153	L1	17.51	110	82.5	115/230	14	1, 30, 65
	1800	215	<b>L3708</b>	2,117	L1	18.64	100	84	230	20.5	1, 30, 65
<b>Totally Enclosed, C-Face, Footless</b>											
2	1800	184C	<b>VL3605</b>	1,309	L1	15.68	64	75.5	115/230	11.5	3, 30
<b>Open Drip Proof, Foot Mount</b>											
1	1800	182	<b>L1401</b>	799	L1	12.75	46	70	115/230	7	30
		182	<b>L1401M</b>	867	L1	12.75	49	70	115/230	7	
	1200	184	<b>L1407</b>	1,401	L1	14.13	64	65	115/230	8	30
1 1/2	1800	184	<b>L1403</b>	892	L1	12.75	56	68	115/230	9.5	30
2	1800	184	<b>L1405</b>	936	L1	14.13	65	71	115/230	12	30
	1200	215	<b>L1503</b>	2,188	L1	15.94	108	68	115/230	14	30
3	1800	215	<b>L1505</b>	1,781	L1	15.94	106	75	115/230	18	30

(a) See notes on inside back flap.