

## Close-coupled pump, three phase, TEFC, footless

1 thru 20 Hp

IP44



### Features:

- Oversize ball bearings for the pump industry
- Locked DE bearing to allow mounting in any configuration
- Suitable for Inverter use per NEMA MG1 Part 31.4.4.2

### Applications:

- General purpose pumps
- Industrial applications
- Commercial pumps
- Food and beverage
- Wastewater
- Agricultural
- Aggregate

Hp	RPM	NEMA Frame	Catalog Number	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
<b>230/460 volts</b>										
1	1800	143JM	VEJMM3546T	PC3	14.43	38	85.5	230/460	1.5	1, 30
1 1/2	1800	145JM	VEJMM3554T	PC3	15.43	45	86.5	230/460	2.2	1, 30
2	1800	145JM	VEJMM3558T	PC3	15.43	44	86.5	230/460	2.9	1, 30
3	1800	182JM	VEJMM3611T	PC3	18.05	74	89.5	230/460	4.2	1, 30
5	1800	184JM	VEJMM3615T	PC3	19.55	90	89.5	230/460	6.7	1, 30
	3600	213JM	VEJMM3709T	PC3	19.76	121	89.5	230/460	9	1, 30
7 1/2	1800	213JM	VEJMM3710T	PC3	20.92	136	91.7	230/460	9.4	1, 30
10	1800	215JM	VEJMM3714T	PC3	22.40	165	91.7	230/460	12	1, 30
15	1800	254JM	VEJMM2333T	PC3	25.28	278	92.4	230/460	18.1	1, 30
20	1800	256JM	VEJMM2334T	PC3	25.28	303	93	230/460	24	1, 30
<b>575 volts</b>										
1	1800	143JM	VEJMM3546T-5	PC3	15.43	38	86.5	575	1.1	1
1 1/2	1800	145JM	VEJMM3554T-5	PC3	16.31	41	86.5	575	1.6	1
2	1800	145JM	VEJMM3558T-5	PC3	15.43	45	86.5	575	2.2	1
3	1800	182JM	VEJMM3611T-5	PC3	18.05	70	89.5	575	3.1	1
5	1800	184JM	VEJMM3615T-5	PC3	19.55	93	89.5	575	5.3	1
7 1/2	1800	213JM	VEJMM3710T-5	PC3	20.92	127	91.7	575	7.6	1, 35
10	1800	215JM	VEJMM3714T-5	PC3	22.42	165	91.7	575	9.6	1, 35
15	1800	254JM	VEJMM2333T-5	PC3	25.28	255	92.4	575	14.6	1, 35
20	1800	256JM	VEJMM2334T-5	PC3	25.28	303	93	575	19.2	1, 35

(a) See notes on inside back flap.

■ Cast iron frame