

## Close-coupled pump, three phase, ODP

1 thru 75 Hp

IP23



### Features:

- Rodent screens to protect against trash debris
- Oversize ball bearings for the pump industry
- Locked DE bearing to allow mounting in any configuration
- Suitable for Inverter use per NEMA MG1 Part 31.4.4.2

### Applications:

- General purpose pumps
- Industrial applications
- Commercial pumps
- Food and beverage
- Wastewater
- Agricultural
- Aggregate

Hp	RPM	NEMA Frame	Catalog Number	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
<b>Foot mounted, 230/460</b>										
1	1800	143JM	<b>EJMM3116T</b>	PC3	13.75	38	85.5	230/460	1.5	1, 30
		143JP	<b>EJPM3116T</b>	PC3	16.81	38	85.5	230/460	1.5	1, 30
1 1/2	3600	143JM	<b>EJMM3120T</b>	PC3	13.75	34	84	230/460	2	1, 30
		145JM	<b>EJMM3154T</b>	PC3	13.75	38	86.5	230/460	2.2	1, 30
	1800	145JP	<b>EJPM3154T</b>	PC3	16.81	37	86.5	230/460	2.2	1, 30
		3600	145JM	<b>EJMM3155T</b>	PC3	13.75	44	85.5	230/460	2.5
2	1800	145JM	<b>EJMM3157T</b>	PC3	14.25	44	86.5	230/460	2.9	1, 30
		145JP	<b>EJPM3157T</b>	PC3	17.31	43	86.5	230/460	2.9	1, 30
	3600	145JM	<b>EJMM3158T</b>	PC3	15.13	49	85.5	230/460	3.8	1, 30
		145JP	<b>EJPM3158T</b>	PC3	17.31	48	85.5	230/460	3.8	1, 30
3	1800	182JM	<b>EJMM3211T</b>	PC3	16.50	72	89.5	230/460	4.2	1, 30
		182JP	<b>EJPM3211T</b>	PC3	19.56	74	89.5	230/460	4.2	1, 30
	3600	182JM	<b>EJMM3212T</b>	PC3	15.12	64	86.5	230/460	6	1, 30
		182JP	<b>EJPM3212T</b>	PC3	18.18	63	86.5	230/460	6	1, 30
5	1800	182TCZ	<b>EWCM3212T</b>	PC3	18.32	63	86.5	230/460	6	1, 30
		184JM	<b>EJMM3218T</b>	PC3	18.00	87	89.5	230/460	6.6	1, 30
	1200	184JP	<b>EJPM3218T</b>	PC3	21.06	92	89.5	230/460	6.6	1, 30
		215JM	<b>EJMM3309T</b>	PC3	19.31	141	89.5	230/460	7.4	1, 30
	3600	184JM	<b>EJMM3219T</b>	PC3	16.50	78	88.5	230/460	8.6	1, 30
		184JP	<b>EJPM3219T</b>	PC3	19.56	77	88.5	230/460	8.6	1, 30
7 1/2	1800	184TCZ	<b>EWCM3219T</b>	PC3	19.69	77	88.5	230/460	8.6	1, 30
		213JM	<b>EJMM3311T</b>	PC3	18.19	120	91	230/460	9.7	1, 30
	1200	213JP	<b>EJPM3311T</b>	PC3	20.94	130	91	230/460	9.3	1, 30
		254JM	<b>EJMM2506T</b>	PC3	24.69	248	90.2	230/460	11	1, 30
	3600	213JM	<b>EJMM3312T</b>	PC3	18.19	120	89.5	230/460	12	1, 30
		213JP	<b>EJPM3312T</b>	PC3	22.07	122	89.5	230/460	12	1, 30
10	1800	213TCZ	<b>EWCM3312T</b>	PC3	21.25	121	89.5	230/460	12	1, 30
		215JM	<b>EJMM3313T</b>	PC3	19.31	136	91.7	230/460	12.5	1, 30
	1200	215JP	<b>EJPM3313T</b>	PC3	23.20	138	91.7	230/460	12.5	1, 30
		256JM	<b>EJMM2511T</b>	PC3	24.69	255	91.7	230/460	14.3	1, 30
	3600	215JM	<b>EJMM3314T</b>	PC3	18.19	131	90.2	230/460	17.5	1, 30
		215JP	<b>EJPM3314T</b>	PC3	22.07	134	90.2	230/460	17.5	1, 30
15	1800	215TCZ	<b>EWCM3314T</b>	PC3	21.25	131	90.2	230/460	17.5	1, 30
		254JM	<b>EJMM2513T</b>	PC3	23.19	214	93	230/460	17.7	1, 30
	1200	254JP	<b>EJPM2513T</b>	PC3	26.06	219	93	230/460	17.7	1, 30
		284JM	<b>EJMM2524T</b>	PC3	24.69	300	91.7	230/460	20.5	1, 30
	3600	254JM	<b>EJMM2514T</b>	PC3	23.19	195	91	230/460	23.5	1, 30
		254JP	<b>EJPM2514T</b>	PC3	26.06	220	91	230/460	23.5	1, 30
20	1800	256JM	<b>EJMM2515T</b>	PC3	23.19	248	93	230/460	23.5	1, 30
		256JP	<b>EJPM2515T</b>	PC3	26.06	236	93	230/460	23.5	1, 30
	3600	256JM	<b>EJMM2516T</b>	PC3	23.19	219	91.7	230/460	28	1, 30
		256JP	<b>EJPM2516T</b>	PC3	26.06	230	91.7	230/460	28	1, 30
25	1800	284JM	<b>EJMM2531T</b>	PC3	25.94	317	93.6	230/460	30	1, 30
		284JP	<b>EJPM2531T</b>	PC3	28.81	335	93.6	230/460	30	1, 30

(a) See notes on inside back flap.

Information

Single phase

General purpose

Severe duty

Large AC

Washdown duty

Explosion proof

Pump

HVAC

Farm duty

## Close-coupled pump, three phase, ODP

Hp	RPM	NEMA Frame	Catalog Number	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
<b>Foot mounted, 230/460 (continued)</b>										
30	3600	284JM	<b>EJMM2534T</b>	PC3	26.56	309	91.7	230/460	33	1, 30
		284JP	<b>EJPM2534T</b>	PC3	29.44	310	91.7	230/460	33	1, 30
	1800	286JM	<b>EJMM2535T</b>	PC3	25.94	359	94.1	230/460	35	1, 30
		286JP	<b>EJPM2535T</b>	PC3	28.81	370	94.1	230/460	35	1, 30
40	3600	286JM	<b>EJMM2538T</b>	PC3	26.56	328	92.4	230/460	45	1, 30
		286JP	<b>EJPM2538T</b>	PC3	29.44	329	92.4	230/460	45	1, 30
	1800	324JM	<b>EJMM2539T</b>	PC3	27.44	417	94.1	230/460	49	1, 30
		324JP	<b>EJPM2539T</b>	PC3	30.31	378	94.1	230/460	47	1, 30
50	3600	324JM	<b>EJMM2542T</b>	PC3	26.94	421	93	230/460	58	1, 30
		324JP	<b>EJPM2542T</b>	PC3	29.81	424	93	230/460	58	1, 30
	1800	326JM	<b>EJMM2543T</b>	PC3	27.94	491	94.5	230/460	57	1, 30
		326JP	<b>EJPM2543T</b>	PC3	30.81	500	94.5	230/460	57	1, 30
60	3600	326JM	<b>EJMM2546T</b>	PC3	26.94	472	93.6	230/460	68	1, 30
	1800	364JP	<b>EJPM2547T</b>	PC3	33.19	565	95	230/460	68	1, 30
75	1800	365JP	<b>EJPM2551T</b>	PC3	36.22	597	95	230/460	87	1, 30
<b>Foot mounted, 575 volts</b>										
3	3600	145JM	<b>EJMM3158T-5</b>	PC3	14.25	48	85.5	575	3	
	1800	182JM	<b>EJMM3211T-5</b>	PC3	16.50	74	89.5	575	3.1	1
5	3600	182JM	<b>EJMM3212T-5</b>	PC3	16.50	63	90.2	575	4.5	
	1800	184JM	<b>EJMM3218T-5</b>	PC3	18.00	92	89.5	575	5.2	1
7 1/2	3600	184JM	<b>EJMM3219T-5</b>	PC3	16.50	77	88.5	575	6.9	1
	1800	213JM	<b>EJMM3311T-5</b>	PC3	18.19	120	91	575	7.4	1, 35
10	3600	213JM	<b>EJMM3312T-5</b>	PC3	19.31	137	91.7	575	9.2	
	1800	215JM	<b>EJMM3313T-5</b>	PC3	18.19	132	91.7	575	10	1
15	3600	215JM	<b>EJMM3314T-5</b>	PC3	19.31	131	90.2	575	14	1
<b>Footless, 230/460</b>										
1	1800	143JM	<b>VEJMM3116T</b>	PC3	14.43	37	85.5	230/460	1.5	1, 30
1 1/2	1800	145JM	<b>VEJMM3154T</b>	PC3	15.43	43	86.5	230/460	2.2	1, 30
2	1800	145JM	<b>VEJMM3157T</b>	PC3	15.43	46	86.5	230/460	2.9	1, 30
3	3600	145JM	<b>VEJMM3158T</b>	PC3	14.25	48	85.5	230/460	3.8	1, 30
	1800	184JM	<b>VEJMM3211T</b>	PC3	18.06	74	89.5	230/460	4.2	1, 30
5	3600	182JM	<b>VEJMM3212T</b>	PC3	16.66	63	86.5	230/460	6	1, 30
	1800	184JM	<b>VEJMM3218T</b>	PC3	19.56	84	89.5	230/460	6.6	1, 30
7 1/2	3600	184JM	<b>VEJMM3219T</b>	PC3	18.04	77	88.5	230/460	8.6	1, 30
	1800	213JM	<b>VEJMM3311T</b>	PC3	19.78	125	91	230/460	9.6	1, 30
10	3600	213JM	<b>VEJMM3312T</b>	PC3	18.19	121	89.5	230/460	12	1, 30
	1800	215JM	<b>VEJMM3313T</b>	PC3	22.41	165	91.7	230/460	12	1, 30
15	3600	215JM	<b>VEJMM3314T</b>	PC3	18.69	131	90.2	230/460	17.5	1, 30
<b>Footless, 575 volts</b>										
1	1800	143JM	<b>VEJMM3116T-5</b>	PC3	15.43	44.00	86.5	575	1.1	
1 1/2	1800	145JM	<b>VEJMM3154T-5</b>	PC3	16.31	51.00	86.5	575	1.6	
2	1800	145JM	<b>VEJMM3157T-5</b>	PC3	16.31	52.00	86.5	575	2.1	
3	1800	182JM	<b>VEJMM3211T-5</b>	PC3	18.06	74.00	89.5	575	3.1	
5	1800	184JM	<b>VEJMM3218T-5</b>	PC3	18.06	77.00	89.5	575	5.2	

(a) See notes on inside back flap.