

Tachometer generators DC, AC and digital output



Flange Mounted



Foot Mounted

Applications: Speed feedback for controls.

Features: Ball bearing construction, UL/CSA approved, IP55, standard mounting C-Face and foot mounted.

Generator Type	Voltage	Catalog Number	Disc. Sym.	Ap'x. Shpg. Wgt.
XPY flange mount (DC)				
XPYIV	50VDC	CMTG50XPYIV	R3B	5.5
XPYIV	100VDC	CMTG100XPYIV	R3B	5.5
XPY foot mount (DC)				
XPYIV	50VDC	FMTG50XPYIV	R3B	6.4
XPYIV	100VDC	FMTG100XPYIV	R3B	6.4
Encoder based digital PY flange mount				
DPY	1024PPR	PTG1024LD (a)	R3B	1
Electrically isolated encoder				
E-ACC	1024PPR	ENC00NV (a)	SVC	2

Notes:

Flange mounted tachs require tach adapters.

XPY tachs have UL/CSA listing, file number E351535.

(a) See Feedback Cable Assemblies for cables.

Red catalog number indicates **NEW** product.