

Stainless steel, three phase, totally enclosed, C-Face, footless 1/3 thru 10 Hp

IP56



Features:

- 300 series stainless steel motor frame, endplates, conduit box, shaft, base, and hardware
- Four condensate drains in each endplate
- Endplate rabbets sealed
- Labyrinth seals on DE and ODE

Applications:

- Food processing
- Packaging
- Pumps and wastewater
- Wet environment

Hp	RPM	NEMA Frame	Enclosure	Catalog Number	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
230/460 volt											
1/3	3600	56C	TENV	VSSWDM3457	WDS	11.09	33	74	208-230/460	0.6	1, 10, 30
	1800	56C	TENV	VSSWDM3534	WDS	11.09	35	75.5	208-230/460	0.7	1,10,12,30
1/2	3600	56C	TENV	VSSWDM3537	WDS	11.09	37	70	208-230/460	0.9	2, 10, 30
	1800	56C	TEFC	VSSFWDM3538	WDS	12.34	40	80	208-230/460	0.9	1,10,12,30
3/4		56C	TENV	VSSWDM3538	WDS	11.09	40	84	230/460	0.9	1, 10, 12, 30
	TEFC		VSSWDM3541	WDS	11.09	41	80	230/460	1.1	1, 10, 12, 30	
	1800	56C	TEFC	VSSFWDM3542	WDS	12.34	44	82.5	208-230/460	1.1	1, 10
		56C	TENV	VSSWDM3542	WDS	11.09	42	82.5	208-230/460	1.1	1, 10
1	1800	56C	TENV	VESSWDM3546	WDS	12.09	44	85.5	230/460	1.5	1,30
		56C	TEFC	VESSFWDM3546	WDS	13.34	39	85.5	230/460	1.5	
		143TC	TEFC	VESSWDM3546T	WDS	13.42	44	87.5	230/460	1.5	1,30
1 1/2	1800	56C	TEFC	VESSWDM3554	WDS	13.34	46	86.5	230/460	2.2	1,30
		145TC	TEFC	VESSWDM3554T	WDS	13.42	45	87.5	230/460	2.1	1,30
2	1800	56C	TEFC	VESSWDM3558	WDS	13.34	48	86.5	230/460	2.8	8, 30
		145TC	TEFC	VESSWDM3558T	WDS	13.42	45	86.5	230/460	2.8	8, 30
3	3600	145TC	TEFC	VESSWDM3559T	WDS	15.67	64	86.5	208-230/460	3.7	1, 30
	1800	182TC	TEFC	VESSWDM3611T	WDS	18.32	60	89.5	230/460	4.2	1,30
5	3600	184TC	TEFC	VESSWDM3613T	WDS	18.32	83	90.2	230/460	5.7	30
	1800	184TC	TEFC	VESSWDM3615T	WDS	18.32	101	89.5	230/460	6.5	30
7 1/2	1800	213TC	TEFC	VESSWDM3710T	WDS	20.16	139	91.7	230/460	9.5	1
10	1800	215TC	TEFC	VESSWDM3714T	WDS	21.66	188	92.4	230/460	12.5	1,30
575 volt											
1	1800	56C	TENV	VESSWDM3546-5	WDS	12.09	39	85.5	575	1.2	
1 1/2	1800	145TC	TEFC	VESSWDM3554T-5	WDS	13.42	45	87.5	575	1.7	1
2	3600	56C	TEFC	VESSWDM3555-5	WDS	14.22	41	86.5	575	2.0	1
	1800	145TC	TEFC	VESSWDM3558T-5	WDS	15.67	56	88.5	575	2.2	8
3	1800	182TC	TEFC	VESSWDM3611T-5	WDS	18.32	83	89.5	575	3.3	1
5	1800	184TC	TEFC	VESSWDM3615T-5	WDS	18.32	112	89.5	575	5.1	1
10	1800	215TC	TEFC	VESSWDM3714T-5	WDS	21.66	191	92.4	575	10.1	1

(a) See notes on inside back flap.

Red catalog number indicates **NEW** product.