

NEW!

Paint free, three phase, totally enclosed, C-Face, 575 volt 1/2 thru 2 Hp

IP55**Features:**

- Sealed ball bearings
- Neoprene gaskets
- Rotating non-contact labyrinth seal
- 300 series stainless steel motor frame, base, shaft and hardware
- No exterior paint

Applications:

- Food processing
- Packaging
- Outdoor applications

Hp	RPM	NEMA Frame	Enclosure	Catalog Number	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
Foot mounted											
1/2	3600	56C	TENV	CSWDM3537-5	WDP	11.06	37	70	575	0.65	2, 10
	1800	56C	TENV	CSWDM3538-5	WDP	11.06	33	80	575	0.7	1, 10, 12
3/4	3600	56C	TENV	CSWDM3541-5	WDP	11.06	39	80	575	0.9	10, 12
	1800	56C	TENV	CSWDM3542-5	WDP	11.06	30	78.5	575	1.1	1, 10, 12
1	1800	56C	TENV	CESWDM3546-5	WDP	12.06	39	85.5	575	1.2	10
		143TC	TENV	CESWDM3546T-5	WDP	12.12	39	85.5	575	1.2	10
1 1/2	1800	56C	TENV	CESWDM3554-5	WDP	12.93	47	86.5	575	1.7	10
		145TC	TENV	CESWDM3554T-5	WDP	12.99	47	86.5	575	1.7	10
2	1800	56C	TENV	CESWDM3558-5	WDP	14.31	56	88.5	575	2.1	10
Footless											
1/2	1800	56C	TENV	VSWDM3538-5	WDP	11.06	33	80	575	0.7	1, 10, 12
3/4	1800	56C	TENV	VSWDM3542-5	WDP	11.06	37	78.5	575	1.1	1, 10, 12
1	1800	56C	TENV	VESWDM3546-5	WDP	12.06	39	85.5	575	1.2	10
		143TC	TENV	VESWDM3546T-5	WDP	12.12	39	85.5	575	1.2	10
1 1/2	1800	56C	TENV	VESWDM3554-5	WDP	12.93	57	86.5	575	1.7	10
		145TC	TENV	VESWDM3554T-5	WDP	12.99	47	86.5	575	1.7	10
2	1800	145TC	TENV	VESWDM3558T-5	WDP	14.37	62	88.5	575	2.1	10

(a) See notes on inside back flap.

Red catalog number indicates **NEW** product.**NEW!**