

Three phase, totally enclosed, foot mounted

1/2 thru 20 Hp

IP55



Features:

- 300 series stainless steel hardware
- Neoprene gaskets
- Double sealed ball bearings
- Lip and V-Ring seal on DE
- White epoxy, corrosion resistant finish
- Stainless steel shaft extension

Applications:

- Food processing
- Wet environment
- Conveyors
- Packaging
- Pumps and wastewater

Hp	RPM	NEMA Frame	Enclosure	Catalog Number	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
1/2	1800	56	TENV	WDM3538	WDW	11.06	27	80	230/460	0.8	1, 12, 30
3/4	1800	56	TENV	WDM3542	WDW	11.06	30	78.5	230/460	1.4	1, 12, 30
1	3600	143T	TENV	EWDM3545T	WDW	11.12	35	82.5	230/460	1.3	1
	1800	56	TENV	EWDM3546	WDW	12.06	39	85.5	230/460	1.5	1, 30
		143T	TENV	EWDM3546T	WDW	12.12	39	85.5	230/460	1.5	1, 30
	1200	145T	TEFC	EWDM3556T	WDW	13.29	41	82.5	230/460	1.8	1
1 1/2	900	182T	TEFC	EWDM3617T	WDW	16.54	65	75.5	230/460	2.3	1
	3600	143T	TENV	EWDM3550T	WDW	12.12	48	85.5	230/460	2	
	1800	145T	TENV	EWDM3554T	WDW	13.00	49	86.5	230/460	2.1	30
	1200	182T	TEFC	EWDM3607T	WDW	16.54	91	87.5	230/460	2.4	1
2	900	184T	TEFC	EWDM3618T	WDW	18.04	95	78.5	230/460	3	1
	3600	145T	TEFC	EWDM3555T	WDW	14.17	50	86.5	230/460	2.5	1
	1800	145T	TEFC	EWDM3558T	WDW	13.29	46	86.5	230/460	2.9	1, 30
	1200	184T	TEFC	EWDM3614T	WDW	18.04	100	88.5	230/460	3.5	1
3	900	213T	TEFC	EWDM3702T	WDW	19.04	111	85.5	230/460	3.5	1
	3600	182T	TEFC	EWDM3610T	WDW	15.17	50	86.5	230/460	3.6	1
	1800	182T	TEFC	EWDM3611T	WDW	16.54	73	89.5	230/460	4.2	1, 30
	1200	213T	TEFC	EWDM3704T	WDW	19.04	139	89.5	230/460	4.6	1
5	900	215T	TEFC	EWDM3705T	WDW	19.04	111	86.5	230/460	5.2	1
	3600	184T	TEFC	EWDM3613T	WDW	16.54	74	88.5	230/460	5.9	1
	1800	184T	TEFC	EWDM3615T	WDW	18.04	90	89.5	230/460	6.7	1, 30
7 1/2	1200	215T	TEFC	EWDM3708T	WDW	20.54	185	89.5	230/460	7.2	1
	3600	213T	TEFC	EWDM3709T	WDW	19.04	129	91.7	230/460	9.5	1
	1800	213T	TEFC	EWDM3710T	WDW	19.04	151	91.7	230/460	9.5	1, 30
10	1200	254T	TEFC	EWDM22976T	WDW	23.57	265	91	230/460	10.7	1
	3600	215T	TEFC	EWDM3711T	WDW	17.89	123	90.2	230/460	11.6	1
	1800	215T	TEFC	EWDM3714T	WDW	20.54	165	91.7	230/460	12	1
15	1200	256T	TEFC	EWDM23932T	WDW	24.57	276	91	230/460	14.7	30
	3600	254T	TEFC	EWDM23994T	WDW	22.32	169	91	230/460	15.3	1
	1800	254T	TEFC	EWDM23933T	WDW	23.57	248	92.4	230/460	18	1, 30
20	3600	256T	TEFC	EWDM41906T	WDW	23.57	242	91	230/460	23	
	1800	256T	TEFC	EWDM23934T	WDW	23.57	269	93	230/460	24	1, 30

(a) See notes on inside back flap.

Red catalog number indicates **NEW** product.

Information

Single phase

General purpose

Severe duty

Large AC

Washdown duty

Explosion proof

Pump

HVAC

Farm duty