

Three phase, totally enclosed, C-Face, foot mounted

1/3 thru 20 Hp

IP55



Features:

- 300 series stainless steel hardware
- Neoprene gaskets
- Double sealed ball bearings
- Lip and V-Ring seal on DE
- White epoxy, corrosion resistant finish
- Stainless steel shaft extension

Applications:

- Food processing
- Wet environment
- Conveyors
- Packaging
- Pumps and wastewater

Hp	RPM	NEMA Frame	Enclosure	Catalog Number	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)	
1/3	1800	56C	TENV	CWDM3534	WDW	11.06	33	75.5	208-230/460	0.7	1	
		56C	TENV	CWDM3537	WDW	11.06	29	70	208-230/460	0.9	1, 12	
	3600	56HC	TENV	CWDM3537-H	WDW	11.91	37	70	208-230/460	0.9	1, 12	
1/2	1800	56C	TENV	CWDM3538	WDW	11.06	28	80	230/460	0.8	1, 12, 30	
		56HC	TENV	CWDM3538-H	WDW	11.91	33	80	230/460	0.8	1, 12	
	1200	56C	TENV	CWDM3539	WDW	12.06	37	78.5	208-230/460	1	1, 12	
		56HC	TENV	CWDM3539-H	WDW	11.91	37	78.5	208-230/460	1	1, 12	
	3600	56C	TENV	CWDM3541	WDW	11.07	35	80	230/460	1.1	1, 12, 30	
		56HC	TENV	CWDM3541-H	WDW	11.91	34	80	230/460	1.1	1, 12	
3/4	1800	56C	TENV	CWDM3542	WDW	11.07	29	78.5	230/460	1.4	1, 12, 30	
		56HC	TENV	CWDM3542-H	WDW	11.91	30	78.5	230/460	1.4	1, 12, 30	
	1200	56C	TENV	CWDM3543	WDW	12.94	46	80	208-230/460	1.4	1	
		56HC	TENV	CWDM3543-H	WDW	12.78	45	81.5	208-230/460	1.4		
		56C	TEFC	CEWDM3545	WDW	12.24	33	77	230/460	1.4	1, 12	
	3600	56C	TENV	CEWDM3545	WDW	11.06	35	82.5	230/460	1.3		
		56HC	TENV	CEWDM3545-H	WDW	11.91	35	82.5	230/460	1.3	1, 12, 30	
		143TC	TENV	CEWDM3545T	WDW	12.12	35	82.5	230/460	1.3	1	
		56C	TENV	CEWDM3546	WDW	12.06	41	85.5	230/460	1.5	30	
1	1800	56HC	TENV	CEWDM3546-H	WDW	11.91	39	85.5	230/460	1.5	1, 30	
		143TC	TENV	CEWDM3546T	WDW	12.13	37	85.5	230/460	1.5	30	
		56C	TEFC	CEWDM3556	WDW	13.24	43	82.5	230/460	1.8	1, 30	
	1200	56HC	TEFC	CEWDM3556-H	WDW	13.08	41	82.5	230/460	1.8	1	
		145TC	TEFC	CEWDM3556T	WDW	13.28	41	82.5	230/460	1.8	1	
		900	182TC	TEFC	CEWDM3617T	WDW	16.54	65	75.5	230/460	2.3	1, 30
	3600	56C	TENV	CEWDM3550	WDW	12.07	46	85.5	230/460	2	1, 30	
		56HC	TENV	CEWDM3550-H	WDW	11.91	48	85.5	230/460	2	1	
		143TC	TENV	CEWDM3550T	WDW	12.12	48	85.5	230/460	2	1	
56C		TENV	CEWDM3554	WDW	12.94	50	86.5	230/460	2.1	30		
1800		56HC	TENV	CEWDM3554-H	WDW	12.78	56	86.5	230/460	2.1		
145TC		TENV	CEWDM3554T	WDW	13.00	48	86.5	230/460	2.1	30		
1 1/2	1200	182TC	TEFC	CEWDM3607T	WDW	16.54	72	87.5	230/460	2.4	1, 30	
		900	184TC	TEFC	CEWDM3618T	WDW	18.04	101	78.5	230/460	3	1
		56HCY	TEFC	CEWDM3555	WDW	13.24	35	85.5	230/460	2.5	1, 30	
	3600	56HC	TEFC	CEWDM3555-H	WDW	13.08	41	85.5	230/460	2.5	1	
		145TC	TEFC	CEWDM3555T	WDW	13.28	45	85.5	230/460	2.5	1, 30	
		56C	TEFC	CEWDM3558	WDW	14.12	48	86.5	230/460	2.9	1, 30	
	2	1800	56HC	TEFC	CEWDM3558-H	WDW	13.96	48	86.5	230/460	2.9	1, 30
			145TC	TEFC	CEWDM3558T	WDW	13.28	46	86.5	230/460	2.9	1, 30
			145TC	TENV	CEWDM3558T	WDW	14.37	54	88.5	230/460	2.7	1, 30
1200		184TC	TEFC	CEWDM3614T	WDW	18.04	93	88.5	230/460	3.5	1, 30	
900		213TC	TEFC	CEWDM3702T	WDW	19.78	111	85.5	230/460	3.5	1	

(a) See notes on inside back flap.

Red catalog number indicates **NEW** product.

Three phase, totally enclosed, C-Face, foot mounted

Hp	RPM	NEMA Frame	Enclosure	Catalog Number	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
3	3600	145TC	TEFC	CEWDM3559T	WDW	14.17	60	86.5	230/460	3.6	1, 30
		182TC	TEFC	CEWDM3610T	WDW	15.18	57	86.5	230/460	3.6	1, 30
	1800	182TC	TEFC	CEWDM3611T	WDW	16.54	78	89.5	230/460	4.2	1, 30
	1200	213TC	TEFC	CEWDM3704T	WDW	19.78	136	89.5	230/460	4.6	1, 30
	900	215TC	TEFC	CEWDM3705T	WDW	19.78	111	86.5	230/460	5.2	1
5	3600	184TC	TEFC	CEWDM3613T	WDW	16.54	80	88.5	230/460	5.9	1, 30
	1800	184TC	TEFC	CEWDM3615T	WDW	18.04	96	89.5	230/460	6.7	1, 30
	1200	215TC	TEFC	CEWDM3708T	WDW	21.27	185	89.5	230/460	7.2	1, 30
7 1/2	3600	184TC	TEFC	CEWDM3616T	WDW	18.04	101	89.5	230/460	8.4	1, 30
		213TC	TEFC	CEWDM3709T	WDW	18.64	143	89.5	230/460	9	1, 30
	1800	213TC	TEFC	CEWDM3710T	WDW	19.78	151	91.7	230/460	9.5	1, 30
10	1200	254TC	TEFC	CEWDM22976T	WDW	23.57	280	91	230/460	11	1, 30
	3600	215TC	TEFC	CEWDM3711T	WDW	18.64	122	90.2	230/460	11.8	1, 30
	1800	215TC	TEFC	CEWDM3714T	WDW	21.27	165	91.7	230/460	12	1
	1200	256TC	TEFC	CEWDM23932T	WDW	23.57	289	91	230/460	15.1	30
15	3600	215TC	TEFC	CEWDM3713T	WDW	21.26	174	91	230/460	17	1, 30
		254TC	TEFC	CEWDM23994T	WDW	21.89	188	91	230/460	16.6	1, 30
	1800	254TC	TEFC	CEWDM23933T	WDW	23.57	256	92.4	230/460	18	1, 30
20	3600	256TC	TEFC	CEWDM41906T	WDW	23.57	274	91	230/460	23	1
	1800	256TC	TEFC	CEWDM23934T	WDW	23.57	283	93	230/460	24	1, 30

(a) See notes on inside back flap.
Red catalog number indicates **NEW** product.

Information

Single phase

General purpose

Severe duty

Large AC

Washdown duty

Explosion proof

Pump

HVAC

Farm duty