

Three phase, totally enclosed, C-Face, 575 volt 1/2 thru 20 Hp

IP55



Features:

- 300 series stainless steel hardware
- Neoprene gaskets
- Double sealed ball bearings
- Lip and V-Ring seal on DE
- White epoxy, corrosion resistant finish
- Stainless steel shaft extension

Applications:

- Food processing
- Wet environment
- Conveyors
- Packaging
- Pumps and wastewater

Hp	RPM	NEMA Frame	Enclosure	Catalog Number	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
Foot mounted											
1/2	1800	56C	TENV	CWDM3538-5	WDW	11.07	26	80	575	0.7	1, 12
3/4	1800	56C	TENV	CWDM3542-5	WDW	11.06	35	78.5	575	1.1	1, 12
1	1800	56C	TENV	CEWDM3546-5	WDW	12.06	39	85.5	575	1.2	
		143TC	TENV	CEWDM3546T-5	WDW	12.12	38	85.5	575	1.2	
1 1/2	1800	145TC	TENV	CEWDM3554T-5	WDW	13.00	46	86.5	575	1.7	1
2	1800	145TC	TEFC	CEWDM3558T-5	WDW	13.28	46	86.5	575	2.3	1
				CEWDM3559T-5	WDW	14.17	52	86.5	575	2.9	1
3	1800	182TC	TEFC	CEWDM3611T-5	WDW	16.54	77	89.5	575	3.3	1
				CEWDM3613T-5	WDW	16.54	70	88.5	575	4.7	1
5	1800	184TC	TEFC	CEWDM3615T-5	WDW	18.04	94	89.5	575	5.3	1
				CEWDM3709T-5	WDW	19.78	143	91	575	7	10
7 1/2	1800	213TC	TEFC	CEWDM3710T-5	WDW	19.78	130	91.7	575	7.6	1
				CEWDM3711T-5	WDW	18.64	122	90.2	575	9.5	10
10	1800	215TC	TEFC	CEWDM3714T-5	WDW	21.27	165	91.7	575	9.6	1
				CEWDM23933T-5	WDW	23.57	258	92.4	575	14.5	1
15	1800	254TC	TEFC	CEWDM23933T-5	WDW	23.57	289	93	575	19	1
20	1800	256TC	TEFC	CEWDM23934T-5	WDW	23.57	289	93	575	19	1
Footless											
1/2	1800	56C	TENV	VWDM3538-5	WDW	11.06	28	80	575	0.7	1, 12
3/4	1800	56C	TENV	VWDM3542-5	WDW	11.06	32	80	575	0.9	1, 12

(a) See notes on inside back flap.

Red catalog number indicates **NEW** product.

Information
Single phase
General purpose
Severe duty
Large AC
Washdown duty
Explosion proof
Pump
HVAC
Farm duty