

**NEW!****Three phase, totally enclosed, C-Face, foot mounted, washdown features**

5 thru 75 Hp

**IP55****Features:**

- 300 series stainless steel hardware
- Neoprene gaskets
- Double sealed ball bearings
- Lip and V-Ring seal on DE
- White epoxy, corrosion resistant finish
- Stainless steel shaft extension
- Rugged cast iron construction

**Applications:**

- Food processing
- Wet environment
- Conveyors
- Packaging
- Pumps and wastewater

Hp	RPM	NEMA Frame	Enclosure	Catalog Number	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
5	900	254TC	TEFC	<b>CEWDM2280T</b>	WDW	23.57	256	86.5	230/460	7.9	1, 30
7 1/2	900	256TC	TEFC	<b>CEWDM2401T</b>	WDW	23.57	320	86.5	230/460	12.1	1
10	900	284TC	TEFC	<b>CEWDM2402T</b>	WDW	27.56	391	89.5	230/460	14.6	1, 30
15	1200	284TC	TEFC	<b>CEWDM4100T</b>	WDW	27.56	447	91.7	230/460	19.4	1
	900	286TC	TEFC	<b>CEWDM2395T</b>	WDW	27.56	455	89.5	230/460	23	1
20	1200	286TC	TEFC	<b>CEWDM4102T</b>	WDW	27.56	429	91.7	230/460	26	1
	900	324TC	TEFC	<b>CEWDM4112T</b>	WDW	30.28	606	90.2	230/460	30	1
25	3600	284TSC	TEFC	<b>CEWDM4107T</b>	WDW	24.57	307	91.7	230/460	29	1
	1800	284TC	TEFC	<b>CEWDM4103T</b>	WDW	27.56	437	93.6	230/460	31	1
	1200	324TC	TEFC	<b>CEWDM4111T</b>	WDW	30.28	605	93	230/460	32	1
30	900	326TC	TEFC	<b>CEWDM4116T</b>	WDW	30.28	606	90.2	230/460	37	1, 30
	3600	286TSC	TEFC	<b>CEWDM4108T</b>	WDW	24.57	299	91.7	230/460	34	1
	1800	286TC	TEFC	<b>CEWDM4104T</b>	WDW	27.56	437	93.6	230/460	38	1
	1200	326TC	TEFC	<b>CEWDM4117T</b>	WDW	30.28	640	93	230/460	39	1
40	900	364TC	TEFC	<b>CEWDM4338T</b>	WDW	33.48	813	91.7	230/460	40	
	3600	324TSC	TEFC	<b>CEWDM4109T</b>	WDW	28.89	470	92.4	230/460	45	1
	1800	324TC	TEFC	<b>CEWDM4110T</b>	WDW	30.28	578	94.1	230/460	48	1
	1200	364TC	TEFC	<b>CEWDM4308T</b>	WDW	33.48	908	94.1	230/460	49.8	
50	900	365TC	TEFC	<b>CEWDM4348T</b>	WDW	33.48	875	91.7	230/460	53	
	3600	326TSC	TEFC	<b>CEWDM4114T</b>	WDW	28.77	575	93	230/460	56	1
	1800	326TC	TEFC	<b>CEWDM4115T</b>	WDW	30.28	700	94.5	230/460	58	1, 30
	1200	365TC	TEFC	<b>CEWDM4312T</b>	WDW	33.48	908	94.1	230/460	61.7	
60	900	405TC	TEFC	<b>CEWDM4458T</b>	WDW	38.20	1216	92.4	230/460	64.3	
	3600	364TSC	TEFC	<b>CEWDM4310T</b>	WDW	31.35	999	93.6	230/460	66.1	
	1800	364TC	TEFC	<b>CEWDM4314T</b>	WDW	33.48	961	95	230/460	70	
	1200	404TC	TEFC	<b>CEWDM4403T</b>	WDW	38.20	1322	94.5	230/460	69.3	
75	900	405TC	TEFC	<b>CEWDM4468T</b>	WDW	38.20	1216	92.4	230/460	78.4	
	3600	365TSC	TEFC	<b>CEWDM4313T</b>	WDW	31.35	1005	94.5	230/460	80.7	
	1800	365TC	TEFC	<b>CEWDM4316T</b>	WDW	33.48	965	95.4	230/460	86	
	1200	405TC	TEFC	<b>CEWDM4404T</b>	WDW	38.20	1322	94.5	230/460	87	
	900	444TC	TEFC	<b>CEWDM4419T</b>	WDW	44.96	1815	93.6	230/460	89.3	

(a) See notes on inside back flap.

■ Cast iron frame

Red catalog number indicates **NEW** product.**NEW!**