

NEW!

Three phase, totally enclosed, foot mounted, washdown features

5 thru 75 Hp

IP55

Information
Single phase
General purpose
Severe duty
Large AC
Washdown duty
Explosion proof
Pump
HVAC
Farm duty



Features:

- 300 series stainless steel hardware
- Neoprene gaskets
- Double sealed ball bearings
- Lip and V-Ring seal on DE
- White epoxy, corrosion resistant finish
- Stainless steel shaft extension
- Rugged cast iron construction

Applications:

- Food processing
- Wet environment
- Conveyors
- Packaging
- Pumps and wastewater

Hp	RPM	NEMA Frame	Enclosure	Catalog Number	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
5	900	254T	TEFC	EWDM2280T	WDW	23.07	320	86.5	230/460	12.1	1, 30
7 1/2	900	256T	TEFC	EWDM2401T	WDW	23.07	320	86.5	230/460	12.1	1
10	900	284T	TEFC	EWDM2402T	WDW	27.56	391	89.5	230/460	14.6	1, 30
15	1200	284T	TEFC	EWDM4100T	WDW	27.56	391	91.7	230/460	21	1
	900	286T	TEFC	EWDM2395T	WDW	27.56	469	89.5	230/460	23	1
20	1200	286T	TEFC	EWDM4102T	WDW	27.56	429	91.7	230/460	26	1
	900	324T	TEFC	EWDM4112T	WDW	30.28	578	90.2	230/460	30	1
25	3600	284TS	TEFC	EWDM4107T	WDW	24.47	265	91.7	230/460	29	1
	1800	284T	TEFC	EWDM4103T	WDW	27.56	437	93.6	230/460	31	1
	1200	324T	TEFC	EWDM4111T	WDW	30.28	605	93	230/460	32	1
	900	326T	TEFC	EWDM4116T	WDW	30.28	578	90.2	230/460	37	1, 30
30	3600	286TS	TEFC	EWDM4108T	WDW	24.47	299	91.7	230/460	34	1
	1800	286T	TEFC	EWDM4104T	WDW	27.56	437	93.6	230/460	38	1
	1200	326T	TEFC	EWDM4117T	WDW	30.28	649	93	230/460	39	1
	900	364T	TEFC	EWDM4338T	WDW	33.48	806	91.7	230/460	40	1
40	3600	324TS	TEFC	EWDM4109T	WDW	28.89	470	92.4	230/460	45	1
	1800	324T	TEFC	EWDM4110T	WDW	30.28	601	94.1	230/460	48	1
	1200	364T	TEFC	EWDM4308T	WDW	33.48	910	94.1	230/460	49.8	1
	900	365T	TEFC	EWDM4348T	WDW	33.48	910	91.7	230/460	52.9	1
50	3600	326TS	TEFC	EWDM4114T	WDW	28.77	575	93	230/460	56	1
	1800	326T	TEFC	EWDM4115T	WDW	30.28	700	87	230/460	57	1
	1200	365T	TEFC	EWDM4312T	WDW	33.48	910	94.1	230/460	61.7	1
	900	405T	TEFC	EWDM4458T	WDW	38.19	1216	92.4	230/460	64.3	1
60	3600	364TS	TEFC	EWDM4310T	WDW	31.35	999	93.6	230/460	66.1	1
	1800	364T	TEFC	EWDM4314T	WDW	33.48	961	95	230/460	70	1
	1200	404T	TEFC	EWDM4403T	WDW	38.19	1322	94.5	230/460	69.3	1
	900	405T	TEFC	EWDM4468T	WDW	38.19	1216	92.4	230/460	78.4	1
75	3600	365TS	TEFC	EWDM4313T	WDW	31.35	1005	94.5	230/460	80.7	1
	1800	365T	TEFC	EWDM4316T	WDW	33.48	965	95.4	230/460	86	1
	1200	405T	TEFC	EWDM4404T	WDW	38.19	1322	94.5	230/460	87	1
	900	444T	TEFC	EWDM4419T	WDW	44.97	1815	93.6	230/460	89.3	1

(a) See notes on inside back flap.

Cast iron frame

Red catalog number indicates **NEW** product.

NEW!