



Basic features

Scope of delivery	Mounting block Nut ISO 4032-M3 (2x) Screw ISO 4762-M3x8 (2x)
Short description	Fixed stop
Use	for inductive sensors BES M8

Environmental conditions

Ambient temperature	-25...100 °C
----------------------------	--------------

Material

Material	Aluminum
Surface protection	anodized, red

Mechanical data

Clamping system	Threads
Dimension	31.8 x 12 x 20 mm
Mounting part	Clamps
Tightening torque	1.5 Nm
Tightening torque max.	1.5 Nm

Remarks

Switching point between the proximity switch and trigger pin can be set wherever needed.