



Basic features

Application	Sensor protection
Scope of delivery	Protective cap
Short description	Sensor cap
Use	For M12 sensors for inductive sensors BES M12 for inductive sensors BES

Environmental conditions

Ambient temperature	-73...260 °C
----------------------------	--------------

Material

Housing material	PTFE, white
Material	PTFE

Mechanical data

Clamping system	Threads
Dimension	Ø 14.7 x 8.9 mm
Inside diameter	12.00 mm
Mounting part	Screws M12
Size	M12x1
Wall thickness t	0.9 mm