



Basic features

Application	Pneumatic flat cylinder with integrated groove Fabco Pancake cylinder
Basic standard	Dimension tolerances: DIN ISO 2768 m
Principle of operation	BMF mounting bracket
Scope of delivery	Fastening screw Mounting bracket Offset screwdriver
Style	Mounting bracket
Use	for magnetic sensors BMF 103

Environmental conditions

Ambient temperature	-40...85 °C
----------------------------	-------------

Material

Housing material	Aluminium
Material	Aluminum

Mechanical data

Dimension	5.8 x 6.8 x 8 mm
Mounting, holder	Threaded pin ISO 4026 M3x3-A2 Offset screwdriver ISO 2936 1.5
Sensor attachment	Cylinder head screw ISO 4762 M2x6-A2 offset screwdriver ISO 2936 1.5
Size	Dovetail slot 6.35
Tightening torque	0.07 Nm
Tightening torque clamping screw	0.2 Nm