



Basic features

Application	Pneumatic cylinder with integrated mounting rail
Basic standard	Dimension tolerances: DIN ISO 2768 m
Principle of operation	BMF mounting bracket
Scope of delivery	Fastening screw Mounting bracket Offset screwdriver
Use	for magnetic sensors BMF 303

Environmental conditions

Ambient temperature	-40...85 °C
----------------------------	-------------

Material

Material	Aluminum
Surface protection	Anodized

Mechanical data

Mounting, holder	Cylinder head screw DIN 7984 M3x6-A2 Offset screwdriver ISO 2936 2.0
Sensor attachment	Threaded pin ISO 4029 M2x4-A2 offset screwdriver ISO 2936 0.9
Size	Dovetail (Bosch)
Tightening torque	0.2 Nm
Tightening torque clamping screw	1.5 Nm

Help Views

