



Basic features

Principle of operation	BTL magnet, rod
------------------------	-----------------

Environmental conditions

Ambient temperature	-40...60 °C
Storage temperature	-40...85 °C

Material

Housing material	PA 6, Ferrite
------------------	---------------

Mechanical data

Application weight	2.00 g
Dimension	Ø 17.2 x 5 mm
Inside diameter	14.0 mm
Mounting part	Clamped
Pressure rating max.	250 bar