



Basic features

|                        |                           |
|------------------------|---------------------------|
| Principle of operation | BTL magnet, rod           |
| Scope of delivery      | Spacer<br>Position sensor |

Environmental conditions

|                     |              |
|---------------------|--------------|
| Ambient temperature | -40...100 °C |
| Storage temperature | -40...100 °C |

Material

|                  |               |
|------------------|---------------|
| Housing material | PA, PO 60, GF |
|------------------|---------------|

Mechanical data

|                      |                          |
|----------------------|--------------------------|
| Application weight   | 10.00 g                  |
| Dimension            | Ø 25 x 8 mm              |
| Inside diameter      | 12.0 mm                  |
| Mounting part        | Through-hole 3.2 mm (2x) |
| Pressure rating max. | 600 bar                  |