



### Basic features

**Principle of operation** BTL magnet, rod

### Environmental conditions

**Ambient temperature** -40...120 °C  
**Storage temperature** -40...120 °C

### Material

**Housing material** Aluminium, Anodized  
**Housing material, surface protection** Anodized

### Mechanical data

**Application weight** 68.00 g  
**Dimension** Ø 65 x 8 mm  
**Inside diameter** 30.0 mm  
**Mounting part** Through-hole 4.3 mm (2x)  
**Pressure rating max.** 600 bar