



1) Reference point, 2) Designation for upper side

Basic features

Principle of operation BTL magnet, float

Environmental conditions

Ambient temperature -20...120 °C

Storage temperature -20...120 °C

Material

Housing material 1.4404 stainless steel

Mechanical data

Application weight 34 g

Dimension $\varnothing 44,0$ mm/ $\varnothing 13,0$ mm x 49,00 mm

Immersion depth at $\rho = 0,7$ g/cm³ approx. 39 mm

Immersion depth at $\rho = 1$ g/cm³ 31 mm

Inside diameter 13,0 mm

Pressure rating max. 20 bar