



1) Reference point

### Basic features

**Principle of operation** BTL magnet, float

### Environmental conditions

**Ambient temperature** -20...120 °C

**Storage temperature** -20...120 °C

### Material

**Housing material** 1.4541 stainless steel

### Mechanical data

**Application weight** 69 g  
**Dimension** Ø 62.00 mm/Ø 16.0 mm x 80.00 mm

**Immersion depth at  $\rho = 0.7 \text{ g/cm}^3$**  approx. 57 mm

**Immersion depth at  $\rho = 1 \text{ g/cm}^3$**  41 mm

**Inside diameter** 16.0 mm

**Pressure rating max.** 15 bar