



Basic features

Application	Assembly
Principle of operation	Capacitive sensor
Scope of delivery	Mounting sight glass rear side Hose clamp Screw B18.6.3 10-32x1.75" (2x) Sensor mounting Sight glass
Use	for sensors $\varnothing 18$ mm
Version	Sight glass, mounting

Environmental conditions

Ambient temperature	-40...85 °C
Storage temperature	-55...121 °C

Material

Housing material	Stainless steel POM
Material	POM Steel, stainless

Mechanical data

Clamping system	Mounting clamp
Dimension	$\varnothing 18 \times 49.8$ mm
Mounting part	Screws, clamps
Size	M18x1
Tightening torque	2.2 Nm
Tightening torque clamping screw	1.1 Nm