



1) Designation for upper side

### Basic features

<b>Principle of operation</b>	BTL magnet, float
<b>Scope of delivery</b>	Cotter pin User manual Floats

### Environmental conditions

<b>Ambient temperature</b>	-20...130 °C
<b>Storage temperature</b>	-20...120 °C

### Material

<b>Housing material</b>	1.4404 stainless steel
-------------------------	------------------------

### Mechanical data

<b>Application weight</b>	30 g
<b>Dimension</b>	Ø 31 mm/Ø 11.7 mm x 69 mm
<b>Immersion depth at <math>\rho = 1 \text{ g/cm}^3</math></b>	53.4 mm
<b>Inside diameter</b>	11.7 mm
<b>Pressure rating max.</b>	4 bar