



1) Fiberglass braided sleeve, 2) Red iron oxide flame protection

Basic features

Scope of delivery	Protective tube
Short description	Silicone-fiberglass tube
Use	for cable guard for weld protection

Material

Material	Glass fiber jacketed Silicone rubber, red
Surface protection	Iron oxide red silicone rubber

Environmental conditions

Ambient temperature	-55...260 °C
----------------------------	--------------

Mechanical data

Dimension	Ø 27.1 x 30480 mm
Size	3/4"

Remarks

GL German Lloyd certified at 800°C for 30 minutes, UL1441- certified, UL VW1-certified for flame resistance, SAE AS1072E- certified for fire protection shell on hoses, MSHA approval for fire protection on hoses in underground mines, DIN 54837/5510-2 railway certified for fire resistance, DIN 5659-2/5510-2 railway certified for low toxicity.