



Basic features

Use	for photoelectric retroreflective sensors
Version	Cube corner 5 mm

Environmental conditions

Ambient temperature	-20...500 °C
----------------------------	--------------

Material

Housing material	Borosilicate crown glass
Material sensing surface	Borosilicate crown glass

Remarks

The degree of reflection is at maximum for vertical light infall.

Mechanical data

Dimension	51 x 95 x 8 mm
Mounting part	Screw M3
Sensing surface	0.3 cm ²

Optical features

Light type	non-polarized light, also for polarized light
-------------------	---