



1) Designation for upper side

Basic features

Principle of operation	BTL magnet, float
Scope of delivery	Floats User manual

Environmental conditions

Ambient temperature	-20...130 °C
Storage temperature	-20...120 °C

Material

Housing material	1.4404 stainless steel
------------------	------------------------

Mechanical data

Application weight	9 g
Dimension	Ø 24.6 mm/Ø 9.5 mm x 32.5 mm
Immersion depth at $\rho = 1 \text{ g/cm}^3$	31.5 mm
Inside diameter	9.5 mm