



Basic features

Short description	Silicone tube
Use	for cable guard for weld protection

Environmental conditions

Ambient temperature	-40...200 °C
----------------------------	--------------

Material

Hardness	60 ±5 Shore A
Material	Silicone 60 white, translucent

Mechanical data

Diameter 2	16.00 mm ±0.8 mm
Diameter tolerance	±0.8 mm
Diameter tolerance	±0.8 mm
Dimension	Ø 19.2 x 16000 mm
Expansion	550 %
Tensile strength	7.0 N/mm ²
Wall thickness t	1.6 mm