



## Basic features

<b>Scope of delivery</b>	Protective hose, 1 roll
<b>Short description</b>	Silicone-fiberglass tube
<b>Use</b>	for cable guard for weld protection

## Environmental conditions

<b>Ambient temperature</b>	-40...250 °C
----------------------------	--------------

## Material

<b>Hardness</b>	35 ±5 Shore A
<b>Material</b>	Glass fiber jacketed Silicone rubber, red

## Mechanical data

<b>Diameter 2</b>	13.00 mm
<b>Dimension</b>	Ø 20 x 15000 mm
<b>Expansion</b>	25 %
<b>Tensile strength</b>	2.76...3.45 N/mm <sup>2</sup>
<b>Wall thickness t</b>	3.5 mm

## Remarks

Flame-retarding  
Maximum temperature at outer jacket from weld spatter/beads short-time 1200°C.