



Basic features

Scope of delivery	Protective hose, 1 roll
Short description	Silicone-fiberglass tube
Use	for cable guard for weld protection

Environmental conditions

Ambient temperature	-40...250 °C
----------------------------	--------------

Material

Hardness	35 ±5 Shore A
Material	Glass fiber jacketed Silicone rubber, red

Mechanical data

Diameter 2	38.00 mm
Dimension	Ø 45 x 15000 mm
Expansion	25 %
Tensile strength	2.76...3.45 N/mm ²
Wall thickness t	3.5 mm

Remarks

Flame-retarding
Maximum temperature at outer jacket from weld spatter/beads short-time 1200°C.