



1) Reference point

Basic features

Principle of operation BTL magnet, float

Environmental conditions

Ambient temperature -20...120 °C

Storage temperature -20...120 °C

Material

Housing material 1.4404 stainless steel

Mechanical data

Application weight 20 g

Dimension Ø 32.00 mm/Ø 11.7 mm x 53.00 mm

Immersion depth at $\rho = 1 \text{ g/cm}^3$ 34 mm

Inside diameter 11.7 mm

Pressure rating max. 24 bar