



3) Threaded pin, 4) not included in scope of delivery, 5) Female, removable, 6) Allen key size 2

Basic features

Scope of delivery	Protective cap
Short description	Protective ring
Use	for inductive sensors BES M8

Environmental conditions

Ambient temperature	-50...650 °C
----------------------------	--------------

Material

Housing material	Stainless steel
Material	1.4401 stainless steel

Mechanical data

Clamping system	Threads
Diameter 2	8.00 mm
Dimension	Ø 15 x 8 mm
Installation	for flush mounting
Mounting part	Threads
Size	M8x1
Wall thickness t	3.5 mm